








SCHEMATIC



RECOMMENDED PCB LAYOUT (TOP VIEW)
GENERAL TOLERANCES: ± 0.05



MALE PLUG SCHEMATIC

NOTES :

1.0) RATING :


- 1.1. VOLTAGE : 12 VDC (R.M.S.)
- 1.2. CURRENT : 1 AMPERE MAXIMUM PER CONTACT AT 30° T-RISE
- 1.3. TEMPERATURE : -25° TO +85°

2.0) ELECTRICAL CHARACTERISTIC

- 2.1. CONTACT RESISTANCE : INITIAL 50m MAX. AFTER 100m
- 2.2. INSULATION RESISTANCE : 100 M MIN.
- 2.3. DIELECTIC WITHSTANDING VOLTAGE : 500 VAC AT SEA LEVEL

3.0) MECHANICAL :

- 3.1. DURABILITY ,MINIMUM: MATED 5000 CYCLES WITHOUT DEGRADING ELECTRICAL
- 3.2. INITIAL:MATING FORCE: 300g~2000g.UNMATING FORCE: 200g~2000g
- 3.3. AFTER LIFE TESTING:MATING FORCE: 300g~2000g.UNMATING FORCE: 200g~2000g

 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY :	DATE :	PART NAME:
	陈一鸣	2014-02-23	3.5耳机座 斜口板上型全插
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY:	DATE :	PART NO.
	马跃	2014-02-23	HYCW-PJ06H65-380B
	APPROVED BY:	DATE :	DRAW NO:
	邱敏	2014-02-23	HYC-2609241554
			SHEET NO.
			1 OF 1