

Features

- Fast switching
- Low turn-on voltage
- PN junction guard ring for transient and ESD protection
- Available in lead free version.

Mechanical Data


- Case: SOT-23
- Terminals: solderable per MIL-STD-202, Method 208

Applications

- surface mount schottky barrier rectifier

Ordering Information

- Shipping Qty:3000/7inch Tape& Reel



Ordering Information

Part Number	Package	Shipping
BAT54	SOT-23	3000 pcs / Tape & Reel
BAT54A	SOT-23	3000 pcs / Tape & Reel
BAT54C	SOT-23	3000 pcs / Tape & Reel
BAT54S	SOT-23	3000 pcs / Tape & Reel

Maximum Ratings (@T_A=25°C unless otherwise specified)

Parameter	Symbol	Limits	Unit
Peak Repetitive Peak reverse voltage	V _{RRM}	30	V
Working Peak Reverse Voltage	V _{RWM}		
DC Reverse Voltage	V _R		
Forward Continuous Current	I _F	200	mA
Repetitive Peak Forward Current	I _{FRM}	300	mA
Forward surge current@t _p <1s	I _{FSM}	600	mA

Thermal Characteristics

Parameter	Symbol	Limits	Unit
Power Dissipation *	P_D	250	mW
Thermal resistance junction to ambient air	$R_{\theta JA}$	500	$^{\circ}\text{C}/\text{W}$
Thermal resistance junction to case	$R_{\theta JC}$	360	$^{\circ}\text{C}/\text{W}$
Junction temperature	T_J	-55 to +125	$^{\circ}\text{C}$
Storage temperature range	T_{STG}	-55 to +150	$^{\circ}\text{C}$

Electrical Characteristics (@ $T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Reverse Breakdown Voltage	$V_{(BR)}$	$I_R=100\mu\text{A}$	30	-	-	V
Forward voltage *1	V_F	$I_F=0.1\text{mA}$	-	-	0.24	V
		$I_F=1\text{mA}$	-	-	0.32	V
		$I_F=10\text{mA}$	-	-	0.40	V
		$I_F=30\text{mA}$	-	-	0.50	V
		$I_F=100\text{mA}$	-	-	0.8	V
Reverse current *2	I_R	$V_R=25\text{V}$	-	-	2	μA
Capacitance Between Terminals	C_T	$V_R=1\text{V}, f=1\text{MHz}$	-	-	10	pF
Reverse Recovery Time	t_{rr}	$I_F=I_R=10\text{mA}$ $I_{rr}=0.1 \times I_R, R_L=100\Omega$	-	-	5	ns
*1: pulse test, $t_p \leq 300\mu\text{s}$ *2: pulse test, $t_p \leq 5\text{ms}$						

Ratings and Characteristic Curves (@ $T_A=25^\circ\text{C}$ unless otherwise specified)




Fig 1 Typical Reverse Characteristic




Fig 2 Typical Forward Characteristics




Fig 3 Capacitance Characteristics





Fig 4 Derating Curve

Package Outline Dimensions (unit: mm)

SOT-23



SOT-23		
Dim	Min	Max
A	2.70	3.10
B	1.10	1.50
C	0.90	1.10
D	0.30	0.50
E	0.35	0.48
G	1.80	2.00
H	0.02	0.10
J	0.05	0.15
K	2.20	2.60

Mounting Pad Layout (unit: mm)

SOT-23

