


Product Summary

- V_{DS} -30 V
- I_{DS} (at $V_{GS}=-10V$) -8 A
- $R_{DS(ON)}$ (at $V_{GS}=-10V$) <21m Ω (TYP)

Application

- Interfacing Switching
- Portable equipment and battery
- Load Switch


Package and Pin Configuration



Top View

SOT23-6

Circuit diagram



Top View

Absolute Maximum Ratings (T_A=25°C unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current	I_D	-8	A
Pulsed Drain Current (t = 100 μ s)	I_{DM}	-50	A
Maximum Power Dissipation	P_D	2.5	W
Operating Junction Temperature Range	T_J	-55 to +150	°C
Storage Temperature Range	T_{stg}	-55 to +150	°C

Thermal Characteristic

PARAMETER	Symbol	Value	Unit
Thermal Resistance from Junction to Ambient(t $\leq$ 10s)	$R_{\theta JA}$	100	°C/W

Note : When mounted on 1" square PCB (FR4 material).

TPSI3421DV-T1-GE3

P-Channel Enhancement Mode MOSFET

WWW.TECHPUB.COM


Electrical Characteristics (T_A=25°C unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Static						
Drain-Source Breakdown Voltage	V _{GS} =0V, I _D = -250μA	BV _{DSS}	-30	--	--	V
Gate-Source Threshold Voltage	V _{DS} =V _{GS} , I _D = -250μA	V _{GS(th)}	-1.0	-1.5	-2.5	V
Gate-Source Leakage	V _{DS} =0V, V _{GS} = ±20V	I _{GSS}	--	--	±100	nA
Zero Gate Voltage Drain Current	V _{DS} = -30V, V _{GS} =0V	I _{DSS}	--	-0.1	-1	μA
	V _{DS} = -30V, T _J =125°C		--	-10	-100	μA
Drain-Source On-State Resistance (Note 1)	V _{GS} = -10V, I _D = -7A	R _{DS(on)}	--	21	27	mΩ
	V _{GS} = -4.5V, I _D = -4A		--	29	37	
Forward Transconductance (Note 2)	V _{DS} = -15V, I _D = -5A	g _{fs}	--	16	--	S
Dynamic (Note 2)						
Total Gate Charge (Note 3)	V _{DS} = -15V,	Q _g	--	12	--	nC
Gate-Source Charge (Note 3)	I _D = - 5A,	Q _{gs}	--	3.5	--	
Gate-Drain Charge (Note 3)	V _{GS} = -4.5V	Q _{gd}	--	3.8	--	
Input Capacitance	V _{DS} = -15V, V _{GS} = 0V, F= 1.0MHz	C _{iss}	--	1030	--	pF
Output Capacitance		C _{oss}	--	125	--	
Reverse Transfer Capacitance		C _{rss}	--	100	--	
Switching						
Turn-On Delay Time (Note 3)	V _{DS} = -10V,	t _{d(on)}	--	28	--	nS
Rise Time (Note 3)	I _D = - 5A,	t _r	--	16	--	
Turn-Off Delay Time (Note 3)	V _{GS} = -4.5V,	t _{d(off)}	--	30	--	
Fall Time (Note 3)	R _{GEN} = 10Ω	t _f	--	10	--	
Source-Drain Diode Ratings and Characteristics (Note 2)						
Forward Voltage	V _{GS} = 0V, I _F = -1A	V _{SD}	--	-0.8	-1.2	V
Continuous Source Current	Integral reverse diode in the MOSFET	I _S	--	--	-8	A
Pulsed Current (Note 1)		I _{SM}	--	--	-50	A


Notes:

1. Pulse test; pulse width ≤ 300 μS, duty cycle ≤ 2%.
2. Guaranteed by design, not subject to production testing.
3. Independent of operating temperature


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current



Capacitance




Gate Charge



On-Resistance vs. Junction Temperature

Package information (Unit: mm)

SOT23-6



Mounting Pad Layout (unit: mm)

