











ITEM	DIM A	形状	DIM B
SATA-04M-22AWB-C21	2.10		2.08
SATA-04M-22AWB-C23	2.30		

SPECIFICATION:

1.MATERIAL:

- 1.1 HOUSING: LCP 30% G/F UL 94V-0
- 1.2 COLOR:BLACK
- 1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm
- 1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

- 2.1 CONTACT:1u" GOLD PLATING ON CONTACT AREA
- 2.2 100u" TIN PLATING ON SOLDER TAILS
- 2.3 30u" NICKEL UNDERPLATING OVER ALL
- 2.4 PEG:100u" TIN PLATING ON SOLDER TAILS
- 2.5 30u" NICKEL UNDERPLATING OVER ALL

环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7+15P 每座板下7.50SMT			
DWN	xiong	PART NO.	SATA-023F-22PS1BY	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY