

承认书

APPROVAL SHEET

客户 CUSTOMER	
客户料号 CUSTOMER P/N	
规格描述 DESCRIPTION	C型螺紋式/250VAC/3~8PF/7A/M3/L30/鍍金
产品编码 PART NUMBER	CL1CGB050TCH740330A1
日期 DATE	2026-08-26

德尔创承认栏 APPROVED BY DERSONIC			客户承认栏 APPROVED BY CUSTOMER	
批 准 APPROVED BY	审 核 CHECK BY	制订 FORMULATE BY	批 准 APPROVED BY	审 核 CHECK BY
彭少雄	吴成愛 样品承认章	胡明康		

东莞市德尔创电子有限公司 DONGGUAN DERSONIC ELECTRONIC CO., LTD.

广东省东莞市寮步镇松湖智谷产业园F2栋15楼

15/F, Blk F2, Songshan Lake Intelligent Valley Industrial Park, Liaobu Town, Dongguan City, PRC



TEL: +86-769-8155 5686

FAX: +86-769-8155 5989

E-mail: sales@dersonic.com

quality@dersonic.com

Website: <http://www.dersonic.com>



产品电性能指标

容量容值	3~8pF
损耗正切	<3%
测试频率	100KHZ
温度 (°C)	25±3
额定电压	250VAC
测试电压	500VAC
额定载流(A)	7
绝缘电阻 250vdc	≥1×103MΩ
温度范围	-55°C+125°C

产品说明:

贯穿滤波器又名穿心电容器是一种三端滤波器, 由于它直接安装在金属屏蔽壳体上, 因此它的接地电感更小, 几乎没有接脚电感影响, 另外它的输入输出端被金属板隔离, 消除了高频耦合, 因此决定了贯穿滤波器具有接近理想 EMI 滤波效果。

螺纹式贯穿滤波器, 外壳端材料为环保铜材, 表面镀层一般采用镀镍、镀银或镀金。外壳安装端为标准螺牙, 一般分为 M3、M4、M5、M6、M8 及英美制牙型等。引线端材料为环保铜材, 表面镀层一般采用镀银或镀金。

	尺寸公差 按图所示	贯穿滤波器
	焊接温度：≤300℃	
	焊接时间：3 秒	尺寸单位：(mm)
	CL1CGB050TCH740330A1	