






RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05



NOTES:

1.MATERIAL:

1.1 HOUSING:LCP 30% G/F UL94V-0

1.2 COLOR:BLACK

1.3 CONTACT:BRASS T=0.25mm

2.FINISH:

2.1 CONTACT:GOLD FLASH PLATING ON CONTACT AREA

2.2 100u"MIN.TIN PLATING ON SOLDERTAILS

2.3 50u"MIN.NICKEL UNDERPLATING OVER ALL

2.4 BOARD LOCK:100u"MIN.TIN PLATING ON SOLDERTAILS

2.5 50u"MIN.NICKEL UNDERPLATING OVEER ALL

3.ELECTRICAL:

3.1 CURRENT RATING:1.5 AMPERE PER CONTACT

3.2 CONTACT RESISTANCE:30 mΩ MAX

3.3 INSULATION RESISTANCE:1000 MΩ MIN

3.4 DIELECTRIC WITH STANDING VOLTAGE:500 VDC

3.5 OPERATING TEMPERATURE: -40°C ~ +85°C

环境要求		产品必须符合ROHS要求					
3	Peg	Brass C2680		Tin/Ni Plated			
2	Terminal	Brass C2680		Gold/Tin Plated			
1	Housing	High Temp	Black	UL 94V-0			
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK			
UNLESS OTHERWISE SPECIFIED TOLERANCES			东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:			TITLE SATA 15P 公座90度DIP型带鱼叉				
X :±0.30	X :±2°		DWN	xiong	PART NO. SATA-019M-15PS1BY		
X.X :±0.20	X.X :±1°		CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10			APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY							