

Description:

This N+P Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.


It can be used in a wide variety of applications.

Features:

N-Channel: $V_{DS}=20V, I_D=20A, R_{DS(on)} < 16m\Omega @ V_{GS}=4.5V$ (Typ: $12m\Omega$)

P-Channel: $V_{DS}=-20V, I_D=-18A, R_{DS(on)} < 30m\Omega @ V_{GS}=-4.5V$ (Typ: $23m\Omega$)

- 1) Low gate charge.
- 2) Green device available.
- 3) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 4) Excellent package for good heat dissipation.



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
DOZ4604A	Z4604A	DFN3*3-8D	5000 pcs/Reel

Absolute Maximum Ratings: ($T_C=25^\circ C$ unless otherwise noted)

Symbol	Parameter	N-Channel	P-Channel	Units
V_{DS}	Drain-Source Voltage	20	-20	V
V_{GS}	Gate-Source Voltage	± 12	± 12	V
I_D	Continuous Drain Current- $T_C=25^\circ C$	20	-18	A
	Continuous Drain Current- $T_C=100^\circ C$	14	-12	
I_{DM}	Pulsed Drain Current ¹	60	-55	A
E_{AS}	Single pulse avalanche energy ²	16	16	mJ
P_D	Power Dissipation - $T_C=25^\circ C$	20.8	20.8	W
$R_{\theta JC}$	Thermal Resistance, Junction to Cast ²	6	6	$^\circ C/W$
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150		$^\circ C$

N-Channel Electrical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourctce Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	20	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =20V	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 12V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	Gate-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	0.5	0.75	1	V
R _{DS(ON)}	Drain-Source On Resistance ³	V _{GS} =4.5V, I _D =4A	---	12	16	m Ω
		V _{GS} =2.5V, I _D =3A	---	16	21	
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =10V, V _{GS} =0V, f=1MHz	---	676.4	---	pF
C _{oss}	Output Capacitance		---	121	---	
C _{rss}	Reverse Transfer Capacitance		---	108.1	---	
Q _g	Gate Charge	V _{GS} =0 to 4.5V , V _{DD} =10V I _D =3A	---	9.45	---	nC
Q _{gs}	Gate-Source Charge		---	1.69	---	
Q _{gd}	Gate-Drain Charge		---	2.62	---	
Switching Characteristics ⁴						
t _{d(on)}	Turn-On Delay Time	V _{DD} =10 V, I _D =3A, R _{REN} =3 Ω ,V _{GS} =4.5V	---	5.25	---	ns
t _r	Rise Time		---	16.8	---	ns
t _{d(off)}	Turn-Off Delay Time		---	24.15	---	ns
t _f	Fall Time		---	7.35	---	ns
Drain-Source Diode Characteristics						
I _S	Continuous Drain to Source Diode	VD=VG=0V	---	----	20	A
I _{SM}	Pulsed Drain to Source Diode ¹	VD=VG=0V	---	---	60	A
V _{SD}	Source-Drain Diode Forward Voltage	V _{GS} =0V, I _S =6.8A	---	---	1.2	V

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature.
2. $R_{\theta JA}$ is measured with the device mounted on a 1inch² pad of 2oz copper FR4 PCB
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$.

N-Typical Characteristics: ($T_C=25^\circ C$ unless otherwise noted)




Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature




Figure 11: Normalized Maximum Transient Thermal Impedance




Figure 12: Peak Current Capacity

P-Channel Electrical Characteristics: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourctce Breakdown Voltage	V _{GS} =0V, I _D =-250 μ A	-20	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =-20V	---	---	-1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =±12V, V _{DS} =0A	---	---	±100	nA
On Characteristics						
V _{GS(th)}	Gate-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =-250 μ A	-0.4	-0.7	-1	V
R _{DS(ON)}	Drain-Source On Resistance ³	V _{GS} =-4.5V, I _D =-4A	---	23	30	m Ω
		V _{GS} =-2.5V, I _D =-3A	---	28	36	
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =-10V, V _{GS} =0V, f=1MHz	---	788.5	---	pF
C _{oss}	Output Capacitance		---	138.6	---	
C _{rss}	Reverse Transfer Capacitance		---	89.25	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} = -10V, I _D =-3.3A V _{GS} = -4.5V, R _{GEN} =1 Ω	---	10.5	---	ns
t _r	Rise Time		---	33.6	---	ns
t _{d(off)}	Turn-Off Delay Time		---	52.5	---	ns
t _f	Fall Time		---	53.55	---	ns
Q _g	Total Gate Charge	V _{GS} =-10V, V _{DD} =-4.5V, I _D =-2A	---	9.24	---	nC
Q _{gs}	Gate-Source Charge		---	1.47	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	1.99	---	nC
Drain-Source Diode Characteristics						
I _S	Continuous Drain to Source Diode	V _D =V _G =0V	---	---	-18	A
I _{SM}	Pulsed Drain to Source Diode ¹		---	---	-55	---
V _{SD}	Source-Drain Diode Forward Voltage	V _{GS} =0V, I _S =-7A	---	---	-1.2	V

P-Typical Characteristics: ($T_C=25^{\circ}\text{C}$ unless otherwise noted)




Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Case Temperature





Figure 11: Maximum Effective Transient Thermal Impedance, Junction-to-Case


DFN3X3-8DPackage Outline Data




Symbol	Min	Typ	Max
A	0.725	0.775	0.825
B	0.28	0.38	0.48
C	0.13	0.15	0.20
D	3.05	3.15	3.25
D1			0.10
E	3.25	3.35	3.45
E1	3.0	3.1	3.2
e	0.60	0.65	0.70
F	0.27	0.32	0.37
H	1.63	1.73	1.83
L	0.93	1.03	1.13

Tape & Reel Information

Dimensions in mm



Symbol	A0	B0	K0	D0	D1	P0	P1	10*P0
Spec	3.55 $\pm$ 0.10	3.45 $\pm$ 0.10	1.13 $\pm$ 0.10	1.55 $\pm$ 0.10	1.55 $\pm$ 0.10	4.00 $\pm$ 0.10	8.00 $\pm$ 0.10	40.0 $\pm$ 0.10
Symbol	W	E	F	P2	t			
Spec	12.00 $\pm$ 0.10	1.75 $\pm$ 0.10	5.50 $\pm$ 0.10	2.00 $\pm$ 0.10	0.20 $\pm$ 0.05			



Pulling direction 

Marking Information:


①:Part NO.

②: Date Code (YWWG / R)

Y: Year Code , last digit of the year

WW : Week Code (01-53)

G/R: G(Green) R(Lead Free)



Previous Version

Version	Date	Subjects (major changes since last revision)
1.2	2026-07-02	Release of final version

Attention :

- Information furnished in this document is believed to be accurate and reliable. However, Shenzhen Doingter Semiconductor Co.,Ltd. assumes no responsibility for the consequences of use without consideration for such information nor use beyond it.
- Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Shenzhen Doingter complies with the agreement. Products and information provided in this document have no infringement of patents.
- Shenzhen Doingter assumes no responsibility for any infringement of other rights of third parties which may result from the use of such products and information. This document supersedes and replaces all information previously supplied.



Is

a registered trademark of Shenzhen Doingter Semiconductor Co., Ltd. Copyright © 2013

Shenzhen Doingter Semiconductor Co.,Ltd. Printed All rights reserved.