










- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-2Y		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X° : ± 2.0°	DR: Yuan Jun Rong		DATE: 2025.02.22	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui		DATE: 2025.02.22	
FINISH:		APPD: Ren An De		DATE: 2025.02.22	
DRAWING NO:		SCALE: N/A		PAGE: 1/1	
		UNITS: mm		REV.: A	

REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria






GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X*: $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-3Y	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X*: $\pm 2.0^{\circ}$	DR: Yuan Jun Rong	DATE: 2025.02.22
.XXX: ± 0.01	.XX*: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 2025.02.22
FINISH:		APPD: Ren An De	DATE: 2025.02.22
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD





- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750℃
 - 8. Matched RoHS criteria



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-4Y		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	DR: Yuan Jun Rong	DATE: 2025.02.22	SCALE: N/A	
FINISH: _____		CHKD: Wu Hui	DATE: 2025.02.22	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD


- NOTES:
1. Rated voltage: 250V AC/DC
 2. Rated current: 7.5A AC/DC
 3. Contact resistance: $\leq 20\text{ m}\Omega$
 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 5. Withstand voltage: 1000V AC/minute
 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : PA66 UL94V-0 750°C
 8. Matched RoHS criteria








GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-8Y	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 2026/06/16
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DATE: 2026/06/16	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		DATE: 2026/06/16	PAGE: 1/1
		APPD: Ren An De	UNITS: mm
			REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria




嵌合状态




嵌合状态


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-12Y	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X°: ± 2.0°	DR: Chen Quan Long	DATE: 2026/06/16
.XXX: ± 0.01	.XX°: ± 1.0°	DATE: 2026/06/16	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD: Ren An De	PAGE: 1/1
		DATE: 2026/06/16	UNITS: mm
			REV.: A




7		8	
REV.	REVISION DESCRIPTION	DATE	



- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
 - 8. Matched RoHS criteria




GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-4R	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:25/09/30
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:25/09/30	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD: Ren An De	DATE:25/09/30
			PAGE: 1/1
			UNITS: mm
			REV.: A





- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-6R		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:25/09/30	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:25/09/30	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE:25/09/30	UNITS: mm	REV.: A
DRAWING NO:					





REV.	REVISION DESCRIPTION	DATE	

- NOTES:
- Rated voltage: 250V AC.DC
 - Rated current: 7.5A AC DC
 - Contact resistance: $\leq 20 \text{ m}\Omega$
 - Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - Withstand voltage: 1000V AC/minute
 - Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - Material : PA66 UL94V-0 750°C
 - Matched RoHS criteria



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-8R	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:26/03/16
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:26/03/16	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		DATE:26/03/16	PAGE: 1/1
		APPD: Ren An De	UNITS: mm
			REV.: A






REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 250V AC/DC
Rated current: 7.5A AC/DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1000V AC/minute
Ambient temperature: -40℃~+105℃
Wire range: AWG#22~#16
Materials: Phosphor bronze, Tin plated

Product name	Dimension mm				适用线规
	A1	B1	A2	B2	AWG#
DTM-T	3.4	2.8	3.2	3.5	22-20
DTM-T-G	4.4	3.4	3.2	3.5	18-16

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-T		TITLE: 4.19mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X°: ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	DR: Chen Quan Long	DATE: 2025.02.22	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE: 2025.02.22	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 250V AC.DC
Rated current: 7.5A AC DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1000V AC/minute
Ambient temprature: -40℃ ~ +105℃
Wire range: AWG#22~#16
Materials: Phosphor bronze, Tin plated

Product name	Dimension mm				适用线规
	A1	B1	A2	B2	AWG#
DTM-RT-G	4.3	3.3	3.2	3.5	18-16
DTM-RT	3.4	2.8	3.2	3.5	22-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-RT		TITLE: 4.19mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X°: ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	DR: Chen Quan Long	DATE: 2025.02.22	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE: 2025.02.22	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A