






客户图纸

NO.	ECN NO.	DESCRIPTION	DATE
1.	D-1	弹力改为55g±5g	2020.12.9



- Note:
- Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
 - Plating(电镀):
Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
Spring: Gold flash (弹簧: 镀金)
 - Electrical(电气特性):
Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12V,2A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
 - Mechanical(机械性能):
Force: 55g±5g at working height. (55g±5g 在工作高度)。
Durability: 10,000 cycles(min) (寿命: 10000次)
 - WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: - 20℃~ + 70℃



RECOMMENDED PCB LAYOUT

深圳市鑫探技术有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	1st Angle
DATE:	2020.12.09	VER.	D.1

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZF0033-21070-02050-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			