












RECOMMENDED P.C.B. LAYOUT (T:0.80mm)
TOLERANCE UNSPECIFIED ±0.05mm

NOTES:

- Material & Finish: See the list;
- Mechanical:
 - Mating force: 5-20Nf;
 - Unmating force: Initial: 8-20Nf; Final: 6-20Nf;
 - Durability: 10000 Cycles;
- Electrical:
 - Current Rating:
VBus Pins: 5A, Vconn Pin: 1.25A, Other Pins: 0.25A;
 - Voltage Rating: 20V Max;
 - Withstanding voltage: 100V AC R.M.S;
 - Contact resistance: 40mΩ Max.;
 - Insulation Resistance: 100MΩ Min.;
- Environmental:
 - Operating temperature: -35°C ~ +85°C;
 - Salt Spray Test: 48H Min. (No oxidation or rust);
 - Wetting Temperature: 265±5°C, 5±0.5s

NO.	PART NAME	Q'TY	MATERIAL	FINISH
5	Shell	1	STAINLESS STEEL, T=0.30mm	50u"Ni Min.
4	Middle Clip	1	STAINLESS STEEL T=0.15mm	No Plating
3	Down Contact	8	COPPER ALLOY, T=0.15mm	Mating area: Au G/F&3u" & 15u" & 30u" Min, Solder Tails: Sn 100u" Min, Underplate: 50u" Min Ni overall
2	Top Contact	8	COPPER ALLOY, T=0.15mm	
1	Housing	1	HIGH TEMPERATURE PLASTIC, UL 94 V-0	Black

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: Type-C Receptacle 16P heighten 4.3H SMT L8.0	
DECIMALS:	ANGLES:	PAR	TYPE-C-638-WSCD43
X.: ±0.50	X': ±5°	DWN	Lucas
X.X: ±0.35	X.X': ±3°	CHKD	Ethan
X.XX: ±0.25	X.XX': ±2.5°	APVD	Jacob
CUSTOMER COPY		SCALE: 1:1	UNIT: MM
		SIZE: A4	SHEET: 1F2
			REV: A



说明:

- 每卷前后各空15PCS,尾部用美纹胶纸封住;
- 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
- 每10卷盘一叠共6000Pcs装入1个外箱内;
- 在搬运过程中要轻拿轻放;
- 在运输中不可堆放过多(1.8M最高),不可重压;
- 跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a.产品不可跑出下带凹槽;
b.产品不可有摔伤,变形;
c.内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
①	TYPE C 16P加高4.3mm母座成品		
①	载带	W=24mm,T=0.40mm	600PCS/盘
②	盖带	W=21.3mm	
③	卷盘	ø380*100*24.4mm	10PCS/箱
④	ROHS标签		10PCS/箱
⑤	产品标签		10PCS/箱
⑥	纸箱	390*390*310mm	6000PCS/箱

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES				
DECIMALS:	ANGLES:	TITLE:Type-C Receptacle 16P heighten 4.3H SMT L8.0		
X.:±0.50	X':±5°	PAR	TYPE-C-638-WSCD43	
X.X:±0.35	X.X':±3°	DWN	Lucas	
X.XX:±0.25	X.XX':±2.5°	CHKD	Ethan	
CUSTOMER COPY		APVD	Jacob	
		SCALE:1:1	UNIT:MM	
		SIZE:A4	SHEET:2F2	REV:A