




Wire Wound Type Common Mode Filter

- 1.High common mode impedance at high frequency cause excellent noise suppression performance.
- 2.ACM3225F2SF series realizes small size and low profile. 3.2x2.5x2.4 mm.
- 3.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 4.Operating temperature-40~ +125 C


Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	IR (Ω) min.
ACM3225F2SF-501T20-CND	500±25%	100	0.10	2000	60	10M
ACM3225F2SF-102T15-CND	1000±25%	100	0.10	1500	60	10M

MECHANICAL




Dimension: mm


SCHEMATICS



IMPEDEANCE FREQUENCY




TAPING AND PACKING



IND1752-J-E

Reel



Dimensions in mm

Quantity (pcs):
2000 PCS PER REEL
3REELS PER CARTON
6000PCS PER CARTON

Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
Tel: 0755-27652992 29016433 E-mail: sales1@cd-tek.com Website: www.cd-tek.com