







RoHS Compliant



NOTES:

1. MATERIAL: SEE "TABLE 1";

2. FINISH: SEE "TABLE 1";

3. ELECTRICAL :

3-1.CONTACT CURRENT RATING :DC 30V 0.5A

3-2.INSULATION RESISTANCE :
100 MEGAOHMS MIN.

3-3.DIELECTRIC WITHSTANDING VOLTAGE :
100VAC MIN.

4.MECHANICAL CHARACTERISTICS :

4-1. MATING FORCE: 3~20N.;


4-2. UNMATING FORCE: 3~20N(INITIAL),2~20N(AFTER 5000 CYCLES);

4-3.DURABILITY : 5,000 MATING CYCLES.


4-4.OPERATING TEMPERATURE : -30°C TO +70°C

TABLE 1:

⑤	弹片端子	1	黄铜	镀亮锡	T=0.15mm
④	弹片端子	1	黄铜	镀亮锡	T=0.15mm
③	弹片端子	1	黄铜	镀亮锡	T=0.15mm
②	弹片端子	1	黄铜	镀亮锡	T=0.15mm
①	主体胶芯	1	PPA	黑色	
NO.	PART NAME	QTY	MATERIAL	DESCRIPTION	REMARK



CIRCUIT DIAGRAM



RECOMMENDED P.C.B
TOP VIEW

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	耳机座		
		料号 (PART NO)	MLD-PJ-320A-4P		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/O	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)	审核 (CHECKED) 邱敏		
图号 (DWG NO)	MLD-2509031032	核准 (APPROVED)	陈镇		