





REV.	REVISION DESCRIPTION	DATE	APPD


- NOTES:
- 1.Rated voltage: 50V AC.DC
 - 2.Rated current: 1A AC DC
 - 3.Contact resistance: ≤30 mΩ
 - 4.Insulation resistance: ≥100 MΩ
 - 5.Withstand voltage: 500V AC/minute
 - 6.Ambient temprature:-40℃~+105℃
 - 7.Material :Nylon UL94V-0 750℃

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE:
.XX: ± 0.15	.X° : ± 2.0°	SHZ-Y-750	1.0mm Pitch Housing
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:24/05/02
FINISH:		CHKD: Wu Hui	DATE:24/05/02
DRAWING NO:		APPD:Ren An De	DATE:24/05/02
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A





REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 50V AC/DC
 - 2. Rated current: 1A AC DC
 - 3. Contact resistance: ≤30 mΩ
 - 4. Insulation resistance: ≥100 MΩ
 - 5. Withstand voltage: 500V AC/minute
 - 6. Ambient temprature: -40℃ ~ +105℃
 - 7. Material :Nylon UL94V-0 750℃
 - 8. Color : Black


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SHZ-Y-750-BK	TITLE: 1.0mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:24/05/02
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:24/05/02	PART NO:
FINISH: _____		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD:Ren An De	PAGE: 1/1
		DATE:24/05/02	UNITS: mm
			REV. : A


REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- Rated voltage: 50V AC.DC
 - Rated current: 1A AC DC
 - Contact resistance: $\leq 30\text{ m}\Omega$
 - Insulation resistance: $\geq 100\text{ M}\Omega$
 - Withstand voltage: 500V AC/minute
 - Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - Wire range: AWG#32~#28
 - Terminal: Phosphor bronze,Tin plated



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: SHZ-T	TITLE: 1.0 mm Pitch Crimp Terminal
.XX: ± 0.2	.X° : ± 2.0°	DR: Chen Quan Long	DATE:21/10/22
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/10/22
FINISH:		APPD:Ren An De	DATE:21/10/22
DRAWING NO:		UNITS: mm	REV.: A0





REV.	REVISION DESCRIPTION	DATE	APPD

- NORES:
- 1. Rated voltage: 50V AC.DC
 - 2. Rated current: 1A AC DC
 - 3. Contact resistance: ≤30 mΩ
 - 4. Insulation resistance: ≥100 mΩ
 - 5. Withstand voltage: 500V AC/minute
 - 6. Ambient temprature: -40℃~+105℃
 - 7. Materials: LCP UL94V-0
 - 8. Matched RoHS criteria

3	③	基座	LCP	1	UL94V-0
2	②	焊片	磷青铜	2	镀锡
1	①	接触件	磷青铜	N*	镀锡
序号	图号	名称	材料	数量	附件

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	SHZ-4AB	1.0	7.0	4.9	2X12	SHZ-24AB	11.0	17.0	14.9
2X3	SHZ-6AB	2.0	8.0	5.9	2X13	SHZ-26AB	12.0	18.0	15.9
2X4	SHZ-8AB	3.0	9.0	6.9	2X14	SHZ-28AB	13.0	19.0	16.9
2X5	SHZ-10AB	4.0	10.0	7.9	2X15	SHZ-30AB	14.0	20.0	17.9
2X6	SHZ-12AB	5.0	11.0	8.9	~	~	~	~	~
2X7	SHZ-14AB	6.0	12.0	9.9	2X20	SHZ-40AB	19.0	25.0	22.9
2X8	SHZ-16AB	7.0	13.0	10.9	~	~	~	~	~
2X9	SHZ-18AB	8.0	14.0	11.9	2X25	SHZ-50AB	24.0	30.0	27.9
2X10	SHZ-20AB	9.0	15.0	12.9	~	~	~	~	~
2X11	SHZ-22AB	10.0	16.0	13.9					

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: SHZ-AB		TITLE: 1.0mm Pitch Wire To Board SMT Wafer	
.XX: ± 0.15	.X°: ± 2.0°			DR:Chen Quan Long DATE:24/05/02	
.XXX: ± 0.01	.XX°: ± 1.0°	FINISH:		PART NO:	
DRAWING NO:		CHKD: Wu Hui DATE:24/05/02		SCALE: N/A	PAGE: 1/1
		APPD:Ren An De DATE:24/05/02		UNITS: mm	REV.: A