








REV.	ECN NO OR DESCRIPTION	REVISED	DATE



RECOMMEND PCB LAYOUT
PCB TOLERANCE: ±0.05

SPECIFICATION:

1.MATERIAL:

- 1.1 HOUSING:LCP UL 94V-0
- 1.2 COLOR:BLACK
- 1.3 CONTACT:BRASS C2680-H,T=0.25mm
- 1.4 PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:

- 2.1 CONTACT:1u"/3u"/5u"/15u"GOLD/TIN PLATING ON CONTACT AREA
- 2.2 100u" TIN PLATING ON SOLDER TAILS
- 2.3 50u" NICKEL UNDERPLATING OVERALL
- 2.4 PEG:100u" TIN PLATING ON SOLDER TAILS
- 2.5 50u" NICKEL UNDERPLATING OVERALL

环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Brass C2680R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE SATA 7P 公座 三面包SMT型(半包开窗)		
X	:±0.30	X	:±2°	DWN xiong PART NO. SATA-016M-07PS1BY
X.X	:±0.20	X.X	:±1°	CHKD lee SCALE:1:1 UNIT: mm
X.XX	:±0.10	APVD wang	SIZE: A4	SHEET:10F 1 REV: A4
CUSTOMER COPY				