


REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	Original reversion	lucky	lucky	Roy	2025/07/18



A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NOTE:

- MECHANICAL:
1-1.MATING FORCE: 5~20N
1-2.UMMATING FORCE: Initial: 8~20N
After 500 to 10,000cycles: 6~20N
1-3.FREQUENCE:500±50 CYCLES/HOUR,10000 CYCLES;
- ELECTRICAL CHARACTERISTICS:
2-1. CURRENT RATING:
VBUS Pins (A4,A9,B4,B9): 5A Max:
1.25 Amps MAX. for Vconn (B5) with return path through the corresponding GND pins(Pin A1, A12, B1, B12).
Other All Pins 0.25A/Pin
2-2. INITIAL CONTACT RESISTANCE:40mΩ Max.
2-3. INSULATION RESISTANCE:100MΩ MIN
2-4. WITHSTANDING VOLTAGE:100V AC,1 MINUTE;
- ENVIRONMENTAL
TEMPERATRUUE RANGE: -40°C TO +85°C.
- Recommended thickness of steel mesh T=0.12mm.

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	Molding	1	NYLON	Black , UL94V-0
2	CONTACT	24	HIGH CONDUCTIVITY COPPER	Contact area: Au 3U
3	MID-PLATE	1	STAINLESS STEEL	RINSE
4	TOP SHELL	1	STAINLESS STEEL	Ni plated over all
5	OUTER SHELL	1	STAINLESS STEEL	Ni plated over all

Unless otherwise specified, other tolerance are:

X ±0.40

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

X* ±5°

X.X* ±4°

X.XX* ±3°

X.XXX* ±2°

PROJ.

UNIT mm

SCALE 1:1

CUSTOMER DRAWING

MUP MUP INDUSTRIAL CO.,LTD.

NAME: **USB Type C Mid-mount Dual-Row SMT Receptacle**

MODEL NO: **MUP-U22015-01**

TYPE : **U4 & 24PIN CH= 1.10**

DRAW Roy 2025/07/18

CHECKED lucky 2025/07/18

APPROVAL lucky 2025/07/18

DWG NO.:

DWG-U22015-01-01

SHEET 1/2

REVISION 1



REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	Original reversion	lucky	lucky	Roy	2025/07/18

NOTES

1. NUMBER OF CONNECTORS:950PCS/REEL
2. LEAD TAPE LENGTH

EMPTY 17PCS	PART 950PCS	EMPTY 17PCS
LEADER 272mm	COMPONENT SUPPLIER	TRAILER 272mm


3. QUANTITY:9500/CARTON

4. WEIGHT :

4.1 NET WEIGHT : X.XX Kg

4.2 GROSS WEIGHT : X.XX Kg

- 5.Meas:350Lx350Wx315H mm



Unless otherwise specified, other tolerance are:			MUP[®] MUP INDUSTRIAL CO.,LTD.		
X	±0.40	X*	±5*	NAME: USB Type C Dual-Row SMT Receptacle	
X.X	±0.30	X.X*	±4*	MODEL NO: MUP-U22015-01	
X.XX	±0.20	X.XX*	±3*	TYPE : U4 & 24PIN CH= 1.10	
X.XXX	±0.10	X.XXX*	±2*		
PROJ.	UNIT	SCALE	DRAW	Roy	2025/07/18
①	mm	1:1	CHECKED	lucky	2025/07/18
CUSTOMER DRAWING			APPROVAL	lucky	2025/07/18
			DWG NO.: DWG-U22015-01-01		
			SHEET 2/2		REVISION 1