


注: 未经批准不得复制、复制或修改, 以及利用其内容进行披露

REV	E.C.N NO.	CONTENT	CHK	DATE



- NOTES1:
- UL Standard
- 1.Rating voltage/current: 300V/20A
 - 2.withstanding voltage: AC2000V/1Min
 - 3.Torque value: M3, 4,43Lbin
 - 4.Wire range: 26~12AWG

IEC Standard

1.	Pollution Degree	3	2	2
Overvoltage Category	III	II	II	
Rate Impulse Voltage(KV)	/	/	/	/
Rate Voltage(V)	/	/	250V	/
Rate Current(A)	/	/	20A	/

2. Torque value: M3, 0.5Nm
3. wire range: 0.2-2.5mm²

NOTES2:





- 1.Housing: PA66(UL94V-0)
- 2.Solder Pin: Copper alloy(Sn Plated)
- 3.Cage: Brass(Ni Plated)
- 4.Screw: Steel(M3,Zn Plated)

NOTES3:

- 1.Pitch: 5.08mm Poles: 02-24P
- 2.Stripping length: 8mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MX129 - 5.08 - XXP - XXXX - XX - X - X



PCB Layout

Pitch Range	In	Nominal Dimension	Range		
mm	In mm			-	□
Over 6	Over 10	Over 30	Over 60	Over 100	Over 150
TO 6	TO 10	TO 30	TO 60	TO 100	TO 150
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	22.09.14	MM	SHEET/OF
CHK.		DATE		SCALE	1:1
APP.		DATE		NAME	MX129-5.08-XXP
				DWGNO.	