

Features

- General rectification
- Low V_F ; Low I_R
- High reliability

PIN	DESCRIPTION
1	Cathode
2	Anode



SOD123



Applications

- surface mount schottky barrier rectifier

Ordering Information

- Shipping Qty:3000/7inch Tape& Reel

Absolute Maximum Ratings (T_A=25°C unless otherwise noted)

Parameter	Symbol		Units
Peak Repetitive Reverse Voltage	V_{RRM}	40	V
RMS Reverse Voltage	V_{RMS}	28	V
Maximum Average Forward Output Current	$I_{F(AV)}$	1	A
Peak Forward Surge Current, 8.3ms Single Half-sine-wave	I_{FSM}	10	A

Thermal Characteristics

Parameter	Symbol			Units
Power Dissipation	P _D	500	250	mW
Typical Thermal Resistance per leg	R _{θJA} *	200	400	°C /W
Operating Junction Temperature Range	T _J	125		°C
Storage Temperature Range	T _{STG}	-55 to +150		°C
* Part mounted on FR-4 board with recommended pad layout				

Electrical Characteristics (T_A=25°C unless otherwise noted)

Parameter	Symbol	Test conditions	Min.	Typ.	Max.	Units
Forward Voltage	V _F *	I _F =1A			0.60	V
		I _F =3A	-	-	0.90	
Maximum Peak Reverse Current	I _R **	V _R = 30V V _R = 40V	-	-	1	mA
Capacitance Between Terminals	C _T	V _R =4V, f=1MHz	-	39	120	pF
*Pulse width ≤380 uS, Duty cycle < 2%						
**pulse test , tp≤5ms						

Typical Electrical Characteristic Curves




Fig.1 Forward Current Derating Curve




Fig.2 Maximum Non-Repetitive Peak Forward Surge Current




Fig.3 Typical Instantaneous Forward Characteristics





Fig.4 Typical Reverse Characteristics

Outline Drawing - SOD123 (unit: mm)



SOD-123		
Dim	Min	Max
A	1.45	1.75
B	2.55	2.85
C	1.00	1.30
D	0.50	0.60
E	0.25	0.45
H	0.02	0.10
J	0.05	0.15
K	3.55	3.85

Mounting Pad Layout-SOD123 (unit: mm)

