





REV.	ECN NO OR DESCRIPTION	REVISED	DATE
1	PROPOSE ONLY	ALLEN	2017.06.04



RECOMMENDED PCB LAYOUT
(TOLERANCE: ±0.05)


Connector Pin Assignment

PIN NO.	NAME	YTP	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)



NOTES:

- ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING:0.5A
DIELECTRIC WITHSTANDING VOLTAGE:AC 500V
INSULATION RESISTANCE:500MΩ MIN
CONTACT RESISTANCE:100mΩ MAX
- ENVIRONMENTAL
TEMPERATURE RANGE: -25°C TO +85°C
MECHANICAL CHARACTERISTICS
MATING CYCLES:5000 INSERTIONS
INSERTION/OUT FORCE:0.1-4.0KGF
- MATERIAL
INSULATOR: HIGH TEMPERATURE PLASTIC UL94V-0
COLOR:BLACK
CONTACT: COPPER ALLOY
SHELL: STAINLESS
SPRING:SWP
- PLATING:
CONTACT
UNDERPLATE: NICKEL 40u".
CONTACT AREA: GOLD FLASH OVER NICKEL 40u".
SOLDER AREA: TIN 80u" MIN OVER NICKEL 40u".
SHELL:PLATE 30u"NICKEL MIN OVER ALL
- PLEASE CONTACT KRCONN SALES REPRESENTATIVE TO VERIFY
PRODUCT DETAILS & AVAILABILITY.



6	SPRING	SUS301-H	1	NO PLATING;
5	CAM FOLLOWER	SUS304-H	1	NO PLATING;
4	SLIDER	SUS301-2/1H+HTN	1	NO PLATING
3	SHELL	SUS301-H	1	Plating Ni 10~50u" over all
2	I/M HSG	PLASTIC	1	BLACK COLOR, UL94 V-0
1	CONTACT	COPPER ALLOY	1	Plating 50u" ~200u" Ni over all, Plating 1u" Min. Au at contact area;
ITEM	PART NAME	MATERIAL	Q'TY	DISCRIPTION

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.5 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



深圳市精睿兴业有限公司
SHENZHEN KRCONN TECHNOLOGY CO., LTD


TITLE	1.85H PUSH Micro SD(TF) CARD CONN.			
DWN	ALLEN	PART NO. TOPP-070208-03G		
CHKD	KEVIN	SCALE:1:1	UNIT: mm	
APVD	ERIC.W	SIZE: A3	SHEET:10F 1	REV: A2

CUSTOMER COPY

REV.	ECN NO OR DESCRIPTION	REVISED	DATE
1	PROPOSE ONLY	ALLEN	2017.06.04

NOTES

- 1.每卷包装数量:1000PCS/每卷
- 2.卷带包装方式:



- 3.每箱包装数量:10000PCS/箱

- 4.纸箱350mm*350mm*340mm(内部尺寸),材质K=K

- 5.10K/箱产品净重: 5.496kg, 毛重: 10.73kg

USER DIRECTION OF FEEDING

客户拉出方向

纸箱底部和顶部各垫一块珍珠棉

护角

纸箱

外箱标签贴示位置

将10卷产品放入箱内

封箱胶带

10 Reels

UNLESS OTHERWISE SPECIFIED TOLERANCES		 深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	1.85H PUSH Micro SD(TF) CARD CONN.		
X :±0.5	X :±2°	DWN	ALLEN	PART NO. TOPP-070208-03G	
X.X :±0.20	X.X :±1°	CHKD	KEVIN	SCALE:1:1	UNIT: mm
X.XX :±0.10		APVD	ERIC.W	SIZE: A3	SHEET:10F 1
CUSTOMER COPY					

