












REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SPECIFICATION:

1MATERIAL:

- 1.1 HOUSING: LCP 30% G/F UL 94V-0
- 1.2 COLOR: BLACK
- 1.3 CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm
- 1.4 PEG: BRASS C2680R H,T=0.30mm
- 1.5 SHELL: spcc,T=0.30mm

2FINISH:

- 2.1 CONTACT: G/F GOLD/TIN PLATING ON CONTACT AREA
- 2.2 100u" MIN. Matte TIN PLATING ON SOLDER TAILS
- 2.3 50u" MIN. NICKEL UNDERPLATING OVERALL

3PEG:100u" MIN. Matte TIN PLATING ON SOLDER TAILS

- 3.1 50u" MIN. NICKEL UNDERPLATING OVERALL

4SHELL:100u" MIN. Matte TIN PLATING ON SOLDER TAILS

- 4.1 50u" MIN. NICKEL UNDERPLATING OVERALL

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7Pin 公座 90°AB 型双柱铁壳成品客户图			
DWN	xiong	PART NO.	SATA-017M-07PS1BY	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY