








剖面 A-A



PCB LAYOUT



剖面 B-B

SPECIFICATION:

MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm

PEG: BRASS C2680R H,T=0.30mm

SHELL: spcc,T=0.30mm

FINISH:

CONTACT:G/F GOLD/TIN PLATING ON CONTACT AREA

100u" MIN. Matte TIN PLATING ON SOLDERTAILS

50u" MIN. NICKEL UNDERPLATING OVERALL

PEG:100u" MIN. Matte TIN PLATING ON SOLDERTAILS

50u" MIN. NICKEL UNDERPLATING OVERALL

SHELL:100u" MIN. Matte TIN PLATING ON SOLDERTAILS

50u" MIN. NICKEL UNDERPLATING OVERALL

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-SATA-01-7PSZG	版本 REV.	A
			X.±0.30	X.*±3°					品名 TITLE	SATA 7P公座双柱 AB型 带铁壳成品	页次 SHEET	1/1
			.X±0.20	.X*±2°	审核 CHECK	EVA			客户料号 CUTM.NO.			
			.XX±0.05	.XX*±0.5°	核准 APPROVAL				JADE			
				单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				