

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD PLATING





ON CONTACT AREA

100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE LEO JOHN	料号 PART NO.	ZX-SATA-04-22PSZMP2	版本 REV.	A
3	Peg	Brass C2680R-H		Tin/Ni Plated				X.	±0.30	X.*	±3°	品名 TITLE	SATA 7+15P 母座 SMT H:4.20 板下型 触式	页次 SHEET	1/1
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				X.X	±0.20	X.X*	±2°	客户料号 CUTM.NO.			
1	Housing	High Temp	Black	UL 94V-0				X.XX	±0.05	X.XX*	±0.5°	核准 APPROVAL			
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK						单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	