



RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATERECOMMENDED PCB LAYOUT(TOP VIEW)
DEFAULT TOLERANCE: ± 0.05

NOTE:

1.MATERIAL:

1.1 INSULATOR: HIGH TEMPERATURE PLASTIC UL 94 V-0;

1.2 CONTACT: COPPER ALLOY

1.3 SHELL: STAINLESS STEEL

2.ELECTRICAL CHARACTERISTICS:

2.1 CONTACT RESISTANCE: $40m\Omega$ Max FOR INITIAL. $10m\Omega$ CHANGE AFTER TEST.
MEASURE AT 20mV, 100mA.

2.2 CONTACT CURRENT RATING: 5A FOR VBUS PIN; 1.25A FOR VCONN PIN.

2.3 DIELECTRIC WITHSTANDING VOLTAGE: 100V AC R.M.S.

2.4 INSULATION RESISTANCE $100M\Omega$ Min2.5 OPERATING TEMPERATURE: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$





3 MECHANICAL CHARACTERISTICS:

3.1 MATING FORCE: 5~20 N.

3.2 UNMATED FORCE: 8~20N AFTER TEST

3.3 DURABILITY: 10,000 CYCLES

4.PLATING

4.1 TERMINAL CONTACT: (SEE TAB) GOLD PLATING 1μ ALL OVER 50μ Min
NICKEL AND 80μ Min Tin ALL OVER 50μ Min NICKEL ON SOLDER AREA4.2 SHELL: 30μ Min. NICKEL ALL OVER,

Signal Name	GND	SSRXp1	SSRXn1	Vbus	SBu2	Dn2	Dp2	CC2	Vbus	SSTXn2	SSTXp2	GND
PIN	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
Signal Name	GND	SSTXp1	SSTXn1	Vbus	CC1	Dp1	Dn1	SBu1	Vbus	SSRXn2	SSRXp2	GND
PIN	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	± 0.35	X'.	$\pm 5^{\circ}$
.X	± 0.30	.X'	$\pm 2^{\circ}$
.XX	± 0.25	.XX'	$\pm 1^{\circ}$
.XXX	± 0.10	.XXX'	$\pm 0.5^{\circ}$

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.





单位	MM	制图	Erick	产品料号	918-418K302AY40001
比例	1:1	审核	L S S	产品名称	USB 3.1 CP 24P 垂直式 13 针长 1.7 50004 系列 中央片带 0.17 间距 无壳无壳 壳位 壳脚 600 PAPT 屏蔽壳 壳 (头部加宽) C7000 端子 合金 10 级 2P
日期	2021/03/10	核准	黄国荣	角法	角法
版本	2021/03/10	版本	VER	版本	A0

RoHS

目錄
MAPX

設定內容
MODIFICATION

日期
DATE



产品放置载带中时，铜合面方向可以不一致！！

包装规范说明:

1. 自动机包装前先调整前段空出15格，中间装300PCS产品，尾端需空出15格；
2. 按照图示方向将成品一一放入REEL包装盘内，依同一方向放入；
3. 一个REEL包装盘放置300个成品，装满成品的REEL盘外圈需贴上保护带，四周贴上美纹胶，盘面贴一张内标签；
4. 将每盘产品依次放入箱内，一箱装10盘(300*10=3000PCS)。四周用三角板固定，最后用透明胶纸将纸箱四周封实，箱外贴上外标签；
5. 若有未装满之零数箱，必须以缓冲材料塞满，数量比较少时可单盘包装出货；
6. 剥离力0.1~1.3KG(300mm/min)，剥离角度:165°~180°；
7. 适用产品:TYPE C 24PIN直立式H12/13四/六脚用

NO.	包材名称 Items	包材料号 Item no	用量 Usage	适用类别 Series	备注 / Remark
①	纸箱 Carton		1		390*390*400mm
②	三角板 FOLDER PAPER BOARD		4		H30mm W7.0mm*3折
③	carrier tape		8		W=32mm PET 透明L=5.38M
④	cover tape				W=25.5MM, 300m/r透明色
⑤	塑胶卷轴 Plastic Reel		10		ø380mm, W=37mm
⑥	干燥剂 Desiccant		4		
⑦	环保标签 Rohs Label		9		
⑧	合格标签 Qualified Label		8		70*60mm
⑨	出货标签 Delivery Label		1		70*60mm

产品图 PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE

X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	918-418K302AY40001
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	USB 3.1 CP 24P直立式H12/13 国牌+六脚脚长1.76透明载带LZTS3T-380(15+300+15)
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	
				版本 VER	A0