






RoHS Compliant



High photosynthesis height(H)	The female seat neight 高度H1	The male seat neight 高度H2	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： 125V, AC 。
4. 接触电阻： $\leq 0.02\Omega$ 。
5. 绝缘电阻： $\geq 100\text{M}\Omega$ 。

Part No	CKT	A	B	C	D	E
LCK-BTY0840-8PSLYR-GO	8	2.40	3.50	5.10	4.20	4.00
LCK-BTY0840-10PSLYR-GO	10	3.20	4.30	5.90	5.00	
LCK-BTY0840-12PSLYR-GO	12	4.00	5.10	6.70	5.80	
LCK-BTY0840-14PSLYR-GO	14	4.80	5.90	7.50	6.60	
LCK-BTY0840-16PSLYR-GO	16	5.60	6.70	8.30	7.40	
LCK-BTY0840-18PSLYR-GO	18	6.40	7.50	9.10	8.20	
LCK-BTY0840-20PSLYR-GO	20	7.20	8.30	9.90	9.00	
LCK-BTY0840-22PSLYR-GO	22	8.00	9.10	10.70	9.80	
LCK-BTY0840-24PSLYR-GO	24	8.80	9.90	11.50	10.60	8.00
LCK-BTY0840-26PSLYR-GO	26	9.60	10.70	12.30	11.40	
LCK-BTY0840-28PSLYR-GO	28	10.40	11.50	13.10	12.20	
LCK-BTY0840-30PSLYR-GO	30	11.20	12.30	13.90	13.00	
LCK-BTY0840-32PSLYR-GO	32	12.00	13.10	14.70	13.80	
LCK-BTY0840-34PSLYR-GO	34	12.80	13.90	15.50	14.60	
LCK-BTY0840-36PSLYR-GO	36	13.6	14.70	16.30	15.40	
LCK-BTY0840-38PSLYR-GO	38	14.40	15.50	17.10	16.20	
LCK-BTY0840-40PSLYR-GO	40	15.20	16.30	17.90	17.00	
LCK-BTY0840-44PSLYR-GO	44	16.80	17.90	19.50	18.60	
LCK-BTY0840-50PSLYR-GO	50	19.20	20.30	21.90	21.00	
LCK-BTY0840-60PSLYR-GO	60	23.20	24.30	25.90	25.00	
LCK-BTY0840-70PSLYR-GO	70	27.20	28.30	29.90	29.00	
LCK-BTY0840-80PSLYR-GO	80	31.20	32.30	33.90	33.00	
LCK-BTY0840-100PSLYR-GO	100	39.20	40.30	41.90	41.00	

MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd																																	
QUADRANT POINT	Ⓚ																																		
TANGENCY POINT	Ⓜ																																		
INTERSECTION POINT	Ⓜ																																		
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		<table border="1"> <tr> <td>DESIGN</td> <td>Andy</td> <td>DATE</td> <td>2014.12.24</td> <td colspan="2">TITLE:</td> </tr> <tr> <td>CHECKED</td> <td></td> <td>DATE</td> <td></td> <td colspan="2">0.8 Pitch 双槽直式BTB插座业务图(单第4.0)</td> </tr> <tr> <td>APPROVED</td> <td></td> <td>DATE</td> <td></td> <td colspan="2"></td> </tr> <tr> <td colspan="4">PART NO: LCK-BTY0840-XXPSLYR-GO</td> <td>REV: 04</td> <td>SCALE: 1:1</td> </tr> <tr> <td colspan="4">DRAWING NO: 102022802</td> <td>SHEET: 1/1</td> <td>UNIT: mm</td> </tr> </table>				DESIGN	Andy	DATE	2014.12.24	TITLE:		CHECKED		DATE		0.8 Pitch 双槽直式BTB插座业务图(单第4.0)		APPROVED		DATE				PART NO: LCK-BTY0840-XXPSLYR-GO				REV: 04	SCALE: 1:1	DRAWING NO: 102022802				SHEET: 1/1	UNIT: mm
DESIGN	Andy	DATE	2014.12.24	TITLE:																															
CHECKED		DATE		0.8 Pitch 双槽直式BTB插座业务图(单第4.0)																															
APPROVED		DATE																																	
PART NO: LCK-BTY0840-XXPSLYR-GO				REV: 04	SCALE: 1:1																														
DRAWING NO: 102022802				SHEET: 1/1	UNIT: mm																														
X. ±0.25																																			
X.xx ±0.20																																			
X.xxx ±0.15																																			
ANGULAR ±3°																																			

序号	品名	材质
①	0.8 Pitch双槽立式 BTB母座胶芯	PA10T UL94 V-0, 颜色:黑色
②	0.8 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式 BTB母座吸盖	LCP UL94 V-0, 颜色:黑色