

RoHS Compliant

SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP 30% G/F UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:










2.1 CONTACT:1u”GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDERTAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDERTAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



ITEM	DIM A	形状	DIM B
SATA-04M-22AWB-C21	2.10		2.08
SATA-04M-22AWB-C23	2.30		

环境要求		产品必须符合ROHS要求			
3	Peg	Brass C2680R—H			Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R—H			Gold/Tin Plated
1	Housing	High Temp		Black	UL 94V—0
NO.	DESCRIPTION	MATERIAL		COLOR	REMARK
MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ±0.25		CHECKED		DATE	
X.x ±0.20		APPROVED		DATE	
X.xx ±0.15		PART NO: LCK—STA—010F22P—BGO			REV: 04
ANGULAR ±3°		DRAWING NO: 102022802			SCALE: 1:1
					UNIT: mm
		SIZE: A4			SHEET: 1/1
					