

PRODUCT CHARACTERISTICS

V_{DS}	145V
$R_{DS(ON)}$ Typ(@ $V_{GS}=10V$)	3m Ω
Qg@typ	125nC
I_D	263A

APPLICATIONS

- * Battery Management
- * Motor Control and Drive
- * Switching Applications

FEATURE

- * Low Gate Charge
- * Low Reverse Transfer Capacitance
- * 100% Avalanche Tested

ORDER INFORMATION

Order Codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT7130E6	TO-263-6L	800 pieces/Reel


ABSOLUTE MAXIMUM RATINGS($T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	V_{DS}	145	V
Gate-Source Voltage	V_{GS}	± 20	V
Drain Current Continuous(@ $V_{GS}=10V$, $T_A=25^{\circ}C$)	I_D	263	A
Drain Current Continuous(@ $V_{GS}=10V$, $T_A=100^{\circ}C$)	I_D	166	A
Drain Current Pulsed	I_{DM}	1052	A
Avalanche Energy *	E_{AS}	1350	mJ
Power Dissipation	P_D	446	W
Junction Temperature	T_J	+150	$^{\circ}C$
Storage Temperature	T_{STG}	-55~ +150	$^{\circ}C$

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Unit
Junction to Ambient	R_{thJA}	42	$^{\circ}C/W$
Junction to Case	R_{thJC}	0.28	$^{\circ}C/W$

Note: * EAS condition: $T_J=25^{\circ}C$, $V_{DD}=50V$, $V_G=10V$, $L=0.5mH$, $R_g=25\Omega$



■ ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Off characteristics						
Drain to Source Breakdown Voltage	V _{DSS}	V _{GS} =0V, I _D =250μA	145	-	-	V
Drain to Source Leakage Current	I _{DSS}	V _{DS} =145V, V _{GS} =0V	-	-	1	μA
Gate to Source Forward Leakage	I _{GSS(F)}	V _{DS} =0V, V _{GS} =+20V	-	-	100	nA
Gate to Source Reverse Leakage	I _{GSS(R)}	V _{DS} =0V, V _{GS} =-20V	-	-	-100	nA
On characteristics						
Drain to Source On-Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =40A	-	3	3.8	mΩ
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =V _{GS} , I _D =250μA	2	2.8	4	V
Dynamic characteristics						
Gate Resistance	R _g	V _{GS} =0V, V _{DS} =0V ,f=1.0MHz	-	4.1	-	Ω
Forward Transconductance	g _{fs}	V _{DS} =10V, I _D =5A	-	31	-	S
Input Capacitance	C _{iss}	V _{DS} =75V, V _{GS} =0V f=1.0MHz	-	8622	-	pF
Output Capacitance	C _{oss}		-	772	-	pF
Reverse Transfer Capacitance	C _{rss}		-	26	-	pF
Resistive Switching Characteristics						
Turn-on Delay Time	t _{d(ON)}	I _D =20A, V _{DS} =75V R _G =3Ω ,V _{GS} =10V	-	32	-	ns
Rise Time	t _r		-	60	-	ns
Turn-off Delay Time	t _{d(OFF)}		-	87	-	ns
Fall Time	t _f		-	48	-	ns
Total Gate Charge	Q _g	I _D =20A, V _{DS} =75V V _{GS} =10V	-	125	-	nC
Gate to Source Charge	Q _{gs}		-	46	-	nC
Gate to Drain("Miller") Charge	Q _{gd}		-	32	-	nC
Source-Drain Diode Characteristics						
Continuous Source Current(Body Diode)	I _s		-	-	263	A
Maximum Pulsed Current(Body Diode)	I _{SM}		-	-	1052	A
Diode Forward Voltage	V _{SD}	I _{SD} =1 A, V _{GS} =0V	-	0.7	1.2	V
Reverse Recovery Time	t _{rr}	I _{SD} =20A, T _j =25 °C	-	114	-	ns
Reverse Recovery Charge	Q _{rr}		dI /dt=100A/μs	-	428	-

■ TYPICAL CHARACTERISTICS




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: $R_{DS(ON)}$ vs. Drain Current




Figure 4: $R_{DS(ON)}$ vs. Junction Temperature




Figure 5: $V_{GS(th)}$ vs. Junction Temperature




Figure 6: $V_{BR(DSS)}$ vs. Junction Temperature

■ TYPICAL CHARACTERISTICS(Cont.)




Figure 7: Body Diode Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Current De-rating




Figure 10: Power De-rating




Figure 11: Maximum Safe Operating Area

■ TO-263-6L PACKAGE OUTLINE DIMENSIONS

