

PRODUCT CHARACTERISTICS

V_{DS}	110V
$R_{DS(ON)}$ Typ(@ $V_{GS}=10V$)	1.1m Ω
Q_g @typ	142nC
I_D	373A

APPLICATIONS

- * Battery Management
- * Motor Control and Drive
- * Switching Applications

FEATURE

- * Low Gate Charge
- * Low Reverse Transfer Capacitance
- * 100% Avalanche Tested

ORDER INFORMATION

Order Codes		Package	Packing
Halogen-Free	Halogen		
MOT1116T4-V	N/A	TOLT	1200 pieces/Reel



ABSOLUTE MAXIMUM RATINGS($T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	V_{DS}	110	V
Gate-Source Voltage	V_{GS}	± 20	V
Drain Current Continuous(@ $V_{GS}=10V, T_c=25^{\circ}C$)	I_D	373	A
Drain Current Continuous(@ $V_{GS}=10V, T_c=100^{\circ}C$)	I_D	263	A
Drain Current Pulsed	I_{DM}	1492	A
Avalanche Energy *	E_{AS}	3400	mJ
Power Dissipation	P_D	415	W
Junction Temperature	T_J	+150	$^{\circ}C$
Storage Temperature	T_{STG}	-55~ +150	$^{\circ}C$

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Unit
Junction to Ambient	R_{thJA}	32.8	$^{\circ}C/W$
Junction to Case	R_{thJC}	0.3	$^{\circ}C/W$

Note: * EAS condition: $T_J=25^{\circ}C, V_{DD}=50V, V_G=10V, L=1mH, R_g=25\Omega$




■ ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$, unless otherwise noted)


Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Off characteristics						
Drain to Source Breakdown Voltage	V _{DSS}	V _{GS} =0V, I _D =250μA	110	-	-	V
Drain to Source Leakage Current	I _{DSS}	V _{DS} =110V, V _{GS} =0V	-	-	1	μA
Gate to Source Forward Leakage	I _{GSS(F)}	V _{DS} =0V, V _{GS} =+20V	-	-	100	nA
Gate to Source Reverse Leakage	I _{GSS(R)}	V _{DS} =0V, V _{GS} =-20V	-	-	-100	nA
On characteristics						
Drain to Source On-Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =20A	-	1.1	1.6	mΩ
		V _{GS} =6V, I _D =20A	-	1.6	2.2	mΩ
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =V _{GS} , I _D =250μA	2	3.2	4	V
Dynamic characteristics						
Gate Resistance	R _g	V _{GS} =0V, V _{DS} =0V , f=1.0MHz	-	1.3	-	Ω
Forward Transconductance	g _{fs}	V _{DS} =10V, I _D =5A	-	30	-	S
Input Capacitance	C _{iss}	V _{DS} =50V, V _{GS} =0V f=1.0MHz	-	12700	-	pF
Output Capacitance	C _{oss}		-	3400	-	pF
Reverse Transfer Capacitance	C _{rss}		-	137	-	pF
Resistive Switching Characteristics						
Turn-on Delay Time	t _{d(ON)}	I _D =50A, V _{DS} =50V R _G =4.5 Ω , V _{GS} =10V	-	36	-	ns
Rise Time	t _r		-	119	-	ns
Turn-off Delay Time	t _{d(OFF)}		-	138	-	ns
Fall Time	t _f		-	120	-	ns
Total Gate Charge	Q _g	I _D =50 A, V _{DS} =50V V _{GS} =10V	-	142	-	nC
Gate to Source Charge	Q _{gs}		-	59	-	nC
Gate to Drain("Miller") Charge	Q _{gd}		-	48	-	nC
Source-Drain Diode Characteristics						
Continuous Source Current(Body Diode)	I _S		-	-	373	A
Maximum Pulsed Current(Body Diode)	I _{SM}		-	-	1492	A
Diode Forward Voltage	V _{SD}	I _{SD} =1A, V _{GS} =0V	-	0.68	1.3	V
Reverse Recovery Time	t _{rr}	I _{SD} =50A, T _J =25 °C dI/dt=100A/μs	-	109	-	ns
Reverse Recovery Charge	Q _{rr}		-	294	-	nC

■ TYPICAL CHARACTERISTICS


Power Capability




Current Capability







Safe Operating Area







Transient Thermal Impedance




■ TYPICAL CHARACTERISTICS(Cont.)



■ TYPICAL CHARACTERISTICS(Cont.)



■ TOLT PACKAGE OUTLINE DIMENSIONS



NOTICE:

- 1、 The information in this document is believed to be accurate and reliable at the time of publication, but is subject to change without notice. Guangdong Renmao Electronics Co., Ltd. ("The Company") reserves the right to modify its products and specifications at any time, and assumes no responsibility for any errors or omissions herein.
- 2、 The Company makes no warranty, express or implied, regarding the fitness of its products for any particular purpose. Customers are responsible for verifying the suitability of the products for their applications and for the design and testing of their end products.
- 3、 The values listed under "Absolute Maximum Ratings" are stress ratings only. Stresses beyond these limits may cause permanent damage to the device.
- 4、 The Company's products are not designed or authorized for use in life support, medical, military, aerospace, or other critical applications where the failure of the product could result in personal injury or death. Any such use is at the customer's own risk.
- 5、 These devices are sensitive to electrostatic discharge (ESD). Proper handling and protection procedures must be observed.
- 6、 No license to any intellectual property right is granted by this document. All products are sold subject to the Company's terms and conditions of sale.