








7		8	
REV.	REVISION DESCRIPTION	DATE	APPD


- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 15A AC DC
 - 3. Contact resistance: ≤20 mΩ
 - 4. Insulation resistance: ≥500 MΩ
 - 5. Withstand voltage: 2000V AC/minute
 - 6. Ambient temprature: -40℃~+105℃
 - 7. Material :Nylon UL94V-0(2)


5		盖板	PA66 UL94V-0	1	绿色	
4		压线框	黄铜	N	镀镍	
3		夹片	磷青铜	N	镀镍	
2		基座	PA66 UL94V-0	1	绿色	
1		螺钉	钢	N	镀锌	M2.5
序号	代号	名称	材质	数量	电镀/颜色	备注

Circuits	Product name	Dimensions (mm)		Circuits	Product name	Dimensions (mm)	
		A	B			A	B
2	2EDG-5.08-2YLS	5.08	10.16	10	2EDG-5.08-10YLS	45.72	50.80
3	2EDG-5.08-3YLS	10.16	15.24	11	2EDG-5.08-11YLS	50.80	55.88
4	2EDG-5.08-4YLS	15.24	20.32	12	2EDG-5.08-12YLS	55.88	60.96
5	2EDG-5.08-5YLS	20.32	25.40	13	2EDG-5.08-13YLS	60.96	66.04
6	2EDG-5.08-6YLS	25.40	30.48	14	2EDG-5.08-14YLS	66.04	71.12
7	2EDG-5.08-7YLS	30.48	35.56	15	2EDG-5.08-15YLS	71.12	76.20
8	2EDG-5.08-8YLS	35.56	40.64	~	~	~	~
9	2EDG-5.08-9YLS	40.64	45.72	24	2EDG-5.08-24YLS	116.84	121.92

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : ± 2.0°	DL50805 (2EDG-5.08)-YLS		5.08 mm Pitch Housing	
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Yuan Jun Rong	DATE: 22/08/01	PART NO:	
FINISH:		CHKD: Wu Hui	DATE: 22/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE: 22/08/01	UNITS: mm	REV.: A








NOTES:

- 1. Rated voltage: 300V AC/DC
- 2. Rated current: 15A AC/DC
- 3. Contact resistance: $\leq 20 \text{ m}\Omega$
- 4. Insulation resistance: $\geq 500 \text{ M}\Omega$
- 5. Withstand voltage: 2000V AC/minute
- 6. Ambient temperature: $-40^\circ\text{C} \sim +105^\circ\text{C}$
- 7. Material :Nylon UL94V-0(2)
- 8. Pin Material : Brass/Nickel Plated

Circuits	Product name	Dimensions(mm)		Circuits	Product name	Dimensions(mm)	
		A	B			A	B
2	2EDG-5.08-2AH	5.08	10.16	10	2EDG-5.08-10AH	45.72	50.80
3	2EDG-5.08-3AH	10.16	15.24	11	2EDG-5.08-11AH	50.80	55.88
4	2EDG-5.08-4AH	15.24	20.32	12	2EDG-5.08-12AH	55.88	60.96
5	2EDG-5.08-5AH	20.32	25.40	13	2EDG-5.08-13AH	60.96	66.04
6	2EDG-5.08-6AH	25.40	30.48	14	2EDG-5.08-14AH	66.04	71.12
7	2EDG-5.08-7AH	30.48	35.56	15	2EDG-5.08-15AH	71.12	76.20
8	2EDG-5.08-8AH	35.56	40.64	~	~	~	~
9	2EDG-5.08-9AH	40.64	45.72	24	2EDG-5.08-24AH	116.84	121.92

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	$X^\circ: \pm 3.0^\circ$	PRODUCT NAME: DL50805(2EDG-5.08)-AH	TITLE: 5.08 mm Pitch Wire To Board DIP Wafer
.XX: ± 0.15	$.X^\circ: \pm 2.0^\circ$	DR: Yuan Jun Rong	DATE: 22/08/01
.XXX: ± 0.01	$.XX^\circ: \pm 1.0^\circ$	CHKD: Wu Hui	DATE: 22/08/01
FINISH:		APPD: Ren An De	DATE: 22/08/01
DRAWING NO:			





REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
1. Rated voltage: 300V AC, DC
 2. Rated current: 15A AC, DC
 3. Contact resistance: $\leq 20\text{ m}\Omega$
 4. Insulation resistance: $\geq 500\text{ M}\Omega$
 5. Withstand voltage: 2000V AC/minute
 6. Ambient temperature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
 7. Material :Nylon UL94V-0(2)
 8. Pin Material : Brass/Nickel Plated

Circuits	Product name	Dimensions(mm)		Circuits	Product name	Dimensions(mm)	
		A	B			A	B
2	2EDG-5.08-2AW	5.08	11.76	10	2EDG-5.08-10AW	45.72	52.40
3	2EDG-5.08-3AW	10.16	16.84	11	2EDG-5.08-11AW	50.80	57.48
4	2EDG-5.08-4AW	15.24	21.92	12	2EDG-5.08-12AW	55.88	62.56
5	2EDG-5.08-5AW	20.32	27.00	13	2EDG-5.08-13AW	60.96	67.64
6	2EDG-5.08-6AW	25.40	32.08	14	2EDG-5.08-14AW	66.04	72.72
7	2EDG-5.08-7AW	30.48	37.16	15	2EDG-5.08-15AW	71.12	77.80
8	2EDG-5.08-8AW	35.56	42.24	~	~	~	~
9	2EDG-5.08-9AW	40.64	47.32	24	2EDG-5.08-24AW	116.84	123.52

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL50805 (2EDG-5.08)-AW	TITLE: 5.08 mm Pitch Wire To Board DIP Wafer
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Yuan Jun Rong	DATE:22/08/01
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:22/08/01
FINISH:		APPD:Ren An De	DATE:22/08/01
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A





- NOTES:
1. Rated voltage: 300V AC/DC
 2. Rated current: 15A AC/DC
 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 4. Insulation resistance: $\geq 500 \text{ M}\Omega$
 5. Withstand voltage: 2000V AC/minute
 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material :Nylon UL94V-0(2)
 8. Pin Material : Brass/Nickel Plated

Circuits	Product name	Dimensions (mm)		Circuits	Product name	Dimensions (mm)	
		A	B			A	B
2	2EDG-5.08-2AWLS	5.08	20.32	10	2EDG-5.08-10AWLS	45.72	60.96
3	2EDG-5.08-3AWLS	10.16	25.40	11	2EDG-5.08-11AWLS	50.80	66.04
4	2EDG-5.08-4AWLS	15.24	30.48	12	2EDG-5.08-12AWLS	55.88	71.12
5	2EDG-5.08-5AWLS	20.32	35.56	13	2EDG-5.08-13AWLS	60.96	76.20
6	2EDG-5.08-6AWLS	25.40	40.64	14	2EDG-5.08-14AWLS	66.04	81.28
7	2EDG-5.08-7AWLS	30.48	45.72	15	2EDG-5.08-15AWLS	71.12	86.36
8	2EDG-5.08-8AWLS	35.56	50.80	~	~	~	~
9	2EDG-5.08-9AWLS	40.64	55.88	24	2EDG-5.08-24AWLS	116.84	132.08

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	$X^{\circ} : \pm 3.0^{\circ}$	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	$.X^{\circ} : \pm 2.0^{\circ}$	DL50805 (2EDG-5.08)-AWLS		5.08 mm Pitch Wire To Board DIP Wafer	
.XXX: ± 0.01	$.XX^{\circ} : \pm 1.0^{\circ}$	DR: Yuan Jun Rong	DATE: 22/08/01	PART NO:	
FINISH:		CHKD: Wu Hui	DATE: 22/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE: 22/08/01	UNITS: mm	REV.: A