


■ Features

- Molding Inductor.
- Low Profile, Low Temp.
- Large Current.
- Customize For Different Need.
- Operating temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (Including self-temperature rise) .

■ Applications

- General Electronic.
- Video Device, TV, TFT.
- Power Module for PC.
- NB/Lap Top Computer.
- Server, VGA Card/Module.

■ Product Identification




(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance: N= $\pm 30\%$, M= $\pm 20\%$, K= $\pm 10\%$

■ Shapes and Dimensions (Unit: mm)



TYPE	A	B	C Max.	D	E	F Ref.	G Ref.	H Ref.
YSPI1365	13.8 Max.	12.6 $\pm$ 0.2	6.5	3.7 $\pm$ 0.5	2.7 $\pm$ 0.5	14.5	5.0	6.5

■ YSPI1365 Series

Part Number	Inductance (μ H) @100KHz/1V	DCR Max. (m Ω)	Saturation Current Isat Typ.(A)	Heat Rating Current Irms Typ.(A)
YSPI1365-R47M	0.47 $\pm$ 20%	1.2	60.0	30.0
YSPI1365-1R0M	1.0 $\pm$ 20%	2.0	36.0	25.0
YSPI1365-1R5M	1.5 $\pm$ 20%	2.5	30.0	20.0
YSPI1365-2R2M	2.2 $\pm$ 20%	4.2	28.0	15.0
YSPI1365-3R3M	3.3 $\pm$ 20%	6.8	25.0	13.0
YSPI1365-4R7M	4.7 $\pm$ 20%	10	21.0	12.0
YSPI1365-5R6M	5.6 $\pm$ 20%	13	18.0	11.5
YSPI1365-6R8M	6.8 $\pm$ 20%	15	16.0	11.0
YSPI1365-8R2M	8.2 $\pm$ 20%	18	15.0	10.5
YSPI1365-100M	10 $\pm$ 20%	20	15.0	9.0
YSPI1365-150M	15 $\pm$ 20%	30	10.5	7.0
YSPI1365-220M	22 $\pm$ 20%	44	7.5	5.8
YSPI1365-270M	27 $\pm$ 20%	50	7.0	5.6
YSPI1365-330M	33 $\pm$ 20%	60	6.5	5.5
YSPI1365-470M	47 $\pm$ 20%	80	7.0	5.0
YSPI1365-680M	68 $\pm$ 20%	130	5.0	3.5
YSPI1365-101M	100 $\pm$ 20%	200	4.5	2.5

※ All test data is referenced to 25 °C ambient.


※ Irms (A):DC current (A) that will cause an approximate ΔT of 40 °C(reference ambient temperature is 25 °C)

※ Isat(A):DC current (A) that will cause L0 to drop approximately 30%.(Internal control standards at 40% MAX)


※ Absolute maximum voltage 30VDC.

■ Current Characteristic


YSPI1365-R47M




YSPI1365-1R0M




YSPI1365-1R5M




YSPI1365-2R2M




YSPI1365-3R3M




YSPI1365-4R7M



YSPI1365-5R6M




YSPI1365-6R8M




■ Current Characteristic


YSPI1365-8R2M




YSPI1365-100M




YSPI1365-150M




YSPI1365-220M




YSPI1365-270M




YSPI1365-330M



YSPI1365-470M




YSPI1365-680M



■ Current Characteristic

YSPI1365-101M



■ General Characteristics

NO.	ITEMS	CONDITIONS	SPECIFICATION
1	OPERATION TEMPERATURE STORAGE TEMPERATURE		-40 ~ +125 °C (INCLUDING COIL TEMPERATURE RISE) -40 ~ +125 °C
2	TEMPERATURE COEFFICIENT	-30 ~ +105 °C	0 ~ 2000ppm/°C
3	FIXING STRENGTH	SAMPLE IS PUSHED IN THREE DIRECTIONS OF X, Y AND Z WITH FORCE OF 5. 0N FOR 10±5 SECONDS. AFTER SOLDERING BETWEEN COPPER PLATE AND ELECTRODES.	NO ELECTRODE DETACHMENT.
4	RESISTANCE TO SOLDERING HEAT TEST	REFER TO THE SPEC "STD-001NP".	NO MECHANICAL BREAKAGE. DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%
5	SOLDERABILITY TEST	IMMERSE THE ELECTRODE IN FLUX FOR 5 SECONDS. THEN DIP THE ELECTRODE INTO A SOLDERING BATH OF 245±5 °C FOR 2±0.5 SECONDS.	OVER 95% OF THE SURFACE BEING IMMersed SHALL BE COVERED WITH NEW SOLDER UNIFORMLY.
6	VIBRATION TEST	AMPLITUDE: 1.5mm P-P FREQUENCY: 10~55~10Hz (1 MINUTE PER CYCLE) DURATION: 1 HOUR IN EACH OF X, Y, Z AXIS.	DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%
7	HUMIDITY TEST	TEMPERATURE: 40 °C ± 2 °C HUMIDITY: 90%~95%RH DURATION: 96±4 HOURS.	DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%
8	THERMAL SHOCK TEST	20 CYCLES OF +105 °C FOR 30 MINUTES, -40 °C FOR 30 MINUTES. CHARACTERISTICS ARE MEASURED AFTER THE AMBIENT AIR EXPOSURE OF 1 HOUR	DEVIATION RELATIVE TO INITIAL VALUE: L: WITHIN ±10%
9	HIGH TEMPERATURE STORAGE TEST	TEMPERATURE: 125 °C ± 2 °C DURATION: 96±4 HOURS	
10	LOW TEMPERATURE STORAGE TEST	TEMPERATURE: -40 °C ± 3 °C DURATION: 96±4 HOURS.	

※ Standard testing conditions:


Unless otherwise specified, the standard range of atmospheric conditions for measurements and tests are as follows:

Ambient temperature: 15 °C ~ 35 °C. Relative humidity : 25% ~ 85%. Air pressure: 86kPa ~ 106kPa.

If there is doubt about the results, measurement shall be made within the following limits:

Ambient temperature: 20 °C ± 1 °C. Relative humidity: 63% ~ 67%. Air pressure: 86kPa ~ 106kPa.

Reflow profile for SMT components




Reflow is referred to standard IPC/ JEDEC J-STD-020D

Profile Feature		Lead(Pb) Free solder
Preheat and soak	• temperature Min.(Ts min)	150°C
	• temperature Max.(Ts max)	200°C
	• time(Tsmin to Ts max)(ts)	60-120 Seconds
Average ramp up rate Tsmax to Tp		3°C/Second Max.
Liquidous temperature (TL)		217 °C
Time (TL) maintained above TL		60-150 seconds
Peak package body temperature (Tp)		Table2
Time (tp)* within 5 °C of the specified classification temperature (Tc)		30* seconds
Average Ramp-down rate (Tp to TL)		6 °C/second max
Time 25 °C to peak temperature		8 minutes max.

Table2. Pb-Free Process - Classification Temperatures (Tc)


Package Thickness	Volume mm3 <350	Volume mm3 350~2000	Volume mm3 >2000
<1.6 mm	260°C	260°C	260°C
1.6mm- 2.5mm	260°C	250°C	245°C
>2.5 mm	250°C	245°C	245°C

■ Taping Dimensions(Unit:mm)




TYPE	W	A	B	C	D	P	K	T	MPQ
YSPI1365	24.0 ± 0.2	12.9 ± 0.1	14.8 ± 0.1	10.75	11.5 ± 0.1	16.0 ± 0.1	6.7 ± 0.1	0.40 ± 0.10	500

■ Reel Dimensions(Unit:mm)




TYPE	W	W1	W2	W3	A	B	C	D
YSPI1365	330 ± 2.0	24.4 ± 2.00	30.4MAX	23.9 Min	13.0 ± 0.50	21.0 ± 0.80	2.0 ± 0.50	100 Min

■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed 300 ± 10 mm/min.