





RoHS Compliant



MICRO SIM

PIN NO.	NAME	PIN NO.	NAME
C1	VCC	C4	VPP
C2	GND	C5	CLK
C3	RST	C6	IO

NOTES:

1. ELECTRICAL CHARACTERISTICS

- 1-1. CONTACT RESISTANCE: 60 Milliohms Max
- 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
- 1-3. VOLTAGE RATING: 50V.
- 1-4. CURRENT RATING: 1.0A.

2. MECHANICAL CHARACTERISTICS

- 2-1. OPERATION TEMPERATURE RANGE: -20°C~+85°C
- 2-2. DURABILITY: 5000 CYCLES

3. MATERIAL:

- 3-1. HOUSING: THERMOPLASTIC,UL 94-V0
- 3-2. TERMINAL: PHOSPHOR BRONZE,T=0.15
- 3-3. SHELL: STAINLESS STEEL,T=0.20

4. FINISHED:

- 4-1. TERMINAL: Ni PLATED UNDER, 3U" Au MIN PLATED ON CONTACT AREA,AU PLATED ON SOLDER TAIL
- 4-2. SHELL: Ni PLATED UNDER,G/F PLATED ON SOLDER TAIL

深圳市敏连达科技有限公司
Shenzhen Minlianda Technology Co.,Ltd.

品名(ITEM NO) MICRO SIM 掀盖1.8H

料号(PART NO) MLD-MICRO SIM-01A

单位(UNIT): MM

未注公差
TOLERANCE UNSPECIFIED

版次(REV): A/0

页次(PAGE):1/1

设计 (DESIGN)

柯南

比例(SCALE) 1:1

X.X ± 0.38
X.XX ± 0.20
X.XXX ± 0.10
X" ± 5"
X.X" ± 2"

模号 (MODEL NO)

审核 (CHECKED)

邱敏

图号 (DWG NO)

MLD-2509031032

核准 (APPROVED)

陈镇