









技术参数:

1. 做用温度: $-25\sim+85^{\circ}\text{C}$;
2. 额定负荷: DC 12V 50mA;
3. 接触电阻: $\leq 50\text{m}\Omega$;
4. 绝缘电阻: $\geq 100\text{M}\Omega$;
5. 耐 压: AC250V (50Hz)/min;
6. 动 作 力: $260\text{g}\pm 50\text{g}$;
7. 使用寿命: 100000次;

帽头H	直径A
3.6	Ø2.4
4.3	Ø2.3
5.0	Ø2.3
6.0	Ø2.3
7.0	Ø2.2
7.5	Ø2.1
8.5	Ø2.1
9.0	Ø2.0
10.0	Ø2.0
11.0	Ø2.0



PCB线路板安装图(±0.1)



电路图

Ordering Information

TC - 4403 * - NH - *G - F* * - 02

系列号 F=防水 CV=护套 SQ=方头 P=带柱 按钮高度 动作力 脚长 默认=K脚 Z=直脚

5	接触脚	H62Y 黄铜	镀银	2	
4	基座	PPA(黑色)	——	1	
3	簧片	不锈钢	镀银	1	
2	盖板	黄铜	Cu/Sn	1	
1	按钮	PPA(黑色)	——	1	
序号	零件名称	材料规格	表面处理	数量	备注

			GENERAL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X.X	±0.30	批 准 APPROVAL	产品名称 TITLE	轻触开关(卧贴 4.5x4.5mm 前插后贴)	版 本 REV.	A
			X.XX	±0.20	比 例 SCALE	产品料号 PART NO.	TC-4403-NH-260G-02	单 位 UNITS	mm
1	初版发行		X.XXX	±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°					