


RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24









SPECIFICATIONS
1.Current rating: 9A AC, DC
2.Voltage rating: 600V AC,DC
3.Temperature range: -25℃ ~ +85℃
4.Insulation resistance: 1000MΩ Min.
5.Withstanding voltage: 1500V AC/ minute.
6.Contact resistance: 10mΩ Max.


Material:
Insulator: Nylon 66 UL 94V-0 （2）
Contact: Phosphor Bronze or Brass
Plating: Plated Tin or Plated Gold
Circuits: 02~06
Mate with XFCN P4202-1xNP series Housing

Ordering Code:
M4202V-1xNP
1 2
1.序列号
2.Pin位数:



CIRCUIT SIZE LAYOUT





P.C.B LAYOUT

PART NO.	Dimensions(mm)	
	A	B
1x02	4.20	9.80
1x03	8.40	14.00
1x04	12.60	18.20
1x05	16.80	22.40
1x06	21.00	26.60

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: M4202V-1xNP

TITLE: 4.20mm Crimp Style Connectors

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.06.28	NONE	1/1	A1

XFCN兴飞连接器
0769-82001899
www.xfconn.com

DWG NO: /