

1

2

3

4

5

6

7

8

SAMZO

REAC/ROHS

REV

ECN NO

DESRPTION

DESIGN

APPROVAL

DATE

A1

NEW

Replace frame

2018.06.12

Term.1 (+)

Mesh/Black

Term.2 (-)

Green Board

6.0

2.2

2.8

0.45

1.Directivity:Omnidirectional

2.Pb contanation Requirement:Lead free

3.Charging type:Diaphragm

4.Sensitivity:-36±3dB (0dB=1V/Pa, 1KHz)

5.Output impedance:Low impedance

6.Standard operating voltage:2V

7.Operating voltage range:1V-10V

8.Current consumptionless :than 500 μA

9.Voltage deduction characteristic:Within 3dB at 1.5V

10.S/N Ratio:More than 58dB(SPL=1Pa,1KHz,A-weighting)

MIC 6022 L2 *1

A

B

C

D

A:Name:Microphone

B: Series:6022

C:Spec-Dip P=:2-2.8

D:Parameter:01-NC/11-SC

-36±3dB

ITEM

DESCRIPTION

MATERIAL

QTY

FINSH/COLOR

D

PCB元件

电容

E

铜环

黄铜/紫铜

1

D

背板

PCB板

1

C

垫圈

硅胶

1

DESIGN

WANGGUIFA

2018.06.12

≥2~5<

±0.25

B

隔膜

聚四氟乙烯

1

CHECKED

ZHENGUILAN

2018.06.12

≥0~2<

±0.15

A

外壳

SPCC

1

镀镍

APPROVED

LILIANJIANG

2018.06.14

≥5

±0.35

FIRST VIEW

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.

WWW.SANCNN.COM

TITLE::

6mm H2.2 插件 无电容/单电容

DWG NO: 6022-P001

PART NO: 6022180122

MODEL NO:MIC6022L2-X1

NAME:

MICROPHONE

SCALE

1:1

UNIT

mm

SAMZO COMPONENTS

Electronic switch and connector manufacturer

1

2

3

4

5

6

7

8