

SAMZO REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12





1.Directivity:Omnidirectional
2.Pb containation Requirement:Lead free
3.Charging type:Diaphragm
4.Sensitivity:-28±3dB（0dB=1V/Pa，1KHz）
5.Output impedance:Low impedance
6.Standard operating voltage:2V
7.Operating voltage range:1V-10V
8.Current consumptionless :than 500 μA
9.Voltage deduction characteristic:Within 3dB at 1.5V
10.S/N Ratio:More than 58dB(SPL=1Pa,1KHz,A-weighting)

MIC 6050 L5 20
Ⓐ Ⓑ Ⓒ Ⓓ

A:Name:Microphone
B: Series:6022
C:Spec-Dip P=:10.0
D:Parameter:DC-28±3dB

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
D	PCB元件	电容		---------					
E	铜环	黄铜/紫铜	1	---------				GENERAL TOLERANCE	
D	背板	PCB板	1	---------				≥0~2<	±0.15
C	垫圈	硅胶	1	---------	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
B	隔膜	聚四氟乙烯	1	---------	CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
A	外壳	SPCC	1	镀镍	APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.SANCNN.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:：6mm H5.0 插件 双电容
DWG NO：6050-P011
PART NO：6050180834
MODEL NO:MIC6050L520
NAME：MICROPHONE