

### Features

- Ultra small package: 1.0x0.6x0.5mm
- Ultra low capacitance: 0.3pF typical
- Ultra low leakage: nA level
- Operating voltage: 5V
- Low clamping voltage
- Complies with following standards:
  - IEC 61000-4-2 (ESD) immunity test
    - Air discharge:  $\pm 20\text{kV}$
    - Contact discharge:  $\pm 20\text{kV}$
  - IEC61000-4-5 (Lightning) 4A (8/20 $\mu\text{s}$ )
- RoHS Compliant




DFN1006-2L

### Mechanical Characteristics

- Package: DFN1006-2L (1.0x0.6x0.5mm)
- Case Material: "Green" Molding Compound.
- Terminal Connections: See Diagram Below
- Marking Information: See Below

### Applications

- Cellular Handsets and Accessories
- Display Ports
- MDDI Ports
- USB Ports
- Digital Visual Interface (DVI)
- PCI Express and Serial SATA Ports



Circuit diagram



Marking (Top View)

### Ordering Information

| Part Number | Packaging         | Reel Size |
|-------------|-------------------|-----------|
| PESD5V0F1BL | 10000/Tape & Reel | 7 inch    |


**Absolute Maximum Ratings ( $T_A=25^{\circ}\text{C}$  unless otherwise specified)**

| Parameter                                                      | Symbol           | Value                | Unit               |
|----------------------------------------------------------------|------------------|----------------------|--------------------|
| Peak Pulse Power (8/20 $\mu\text{s}$ )                         | Ppk              | 100                  | W                  |
| Peak Pulse Current (8/20 $\mu\text{s}$ )                       | I <sub>PP</sub>  | 4                    | A                  |
| ESD per IEC 61000-4-2 (Air)<br>ESD per IEC 61000-4-2 (Contact) | V <sub>ESD</sub> | $\pm 20$<br>$\pm 20$ | kV                 |
| Operating Temperature Range                                    | T <sub>J</sub>   | -55 to +125          | $^{\circ}\text{C}$ |
| Storage Temperature Range                                      | T <sub>stg</sub> | -55 to +150          | $^{\circ}\text{C}$ |


**Electrical Characteristics ( $T_A=25^{\circ}\text{C}$  unless otherwise specified)**

| Parameter               | Symbol           | Min | Typ | Max | Unit          | Test Condition                                    |
|-------------------------|------------------|-----|-----|-----|---------------|---------------------------------------------------|
| Reverse Working Voltage | V <sub>RWM</sub> |     |     | 5   | V             |                                                   |
| Breakdown Voltage       | V <sub>BR</sub>  | 6.5 |     | 9.5 | V             | I <sub>T</sub> = 1mA                              |
| Reverse Leakage Current | I <sub>R</sub>   |     |     | 0.2 | $\mu\text{A}$ | V <sub>RWM</sub> = 5V                             |
| Clamping Voltage        | V <sub>C</sub>   |     |     | 12  | V             | I <sub>PP</sub> = 1A (8 x 20 $\mu\text{s}$ pulse) |
| Clamping Voltage        | V <sub>C</sub>   |     |     | 25  | V             | I <sub>PP</sub> = 4A (8 x 20 $\mu\text{s}$ pulse) |
| Junction Capacitance    | C <sub>J</sub>   |     | 0.3 | 0.5 | pF            | V <sub>R</sub> = 0V, f = 1MHz                     |


## Typical Performance Characteristics (TA=25°C unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current



Power Derating Curve



8 X 20μs Pulse Waveform




Note: Data is taken with a 10x attenuator

ESD Clamping Voltage


8 kV Contact per IEC61000-4-2

## DFN1006-2L Package Outline Drawing



| SYM | DIMENSIONS  |      |      |           |       |       |
|-----|-------------|------|------|-----------|-------|-------|
|     | MILLIMETERS |      |      | INCHES    |       |       |
|     | MIN         | NOM  | MAX  | MIN       | NOM   | MAX   |
| A   | 0.45        | 0.50 | 0.55 | 0.018     | 0.020 | 0.022 |
| A1  | 0.00        | 0.02 | 0.05 | 0.000     | 0.001 | 0.002 |
| b   | 0.45        | 0.50 | 0.55 | 0.018     | 0.020 | 0.022 |
| c   | 0.12        | 0.15 | 0.18 | 0.005     | 0.006 | 0.007 |
| D   | 0.95        | 1.00 | 1.05 | 0.037     | 0.039 | 0.041 |
| e   | 0.65 BSC    |      |      | 0.026 BSC |       |       |
| E   | 0.55        | 0.60 | 0.65 | 0.022     | 0.024 | 0.026 |
| L   | 0.20        | 0.25 | 0.30 | 0.008     | 0.010 | 0.012 |
| L1  | 0.05REF     |      |      | 0.002REF  |       |       |
| h   | 0.07        | 0.12 | 0.17 | 0.003     | 0.005 | 0.007 |

## Suggested Land Pattern



| SYM | DIMENSIONS  |        |
|-----|-------------|--------|
|     | MILLIMETERS | INCHES |
| X   | 0.60        | 0.024  |
| Y1  | 0.50        | 0.020  |
| Y2  | 0.30        | 0.012  |
| Y3  | 0.80        | 0.032  |
| Z   | 1.30        | 0.052  |