

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	NEW DRAWING	2026.06.10	Janus

SPECIFICATION:

Electrical:

- Current Rating:1.5Amp MAX. @25℃
- Voltage Rating:150VAC MAX.
- Insulation Resistance:500 Megohms MIN.
- Contact Resistance:20 milliohms MAX.(Initial)
- Withstanding Voltage:
Contact to Contact: 1,000 VDC or AC Peak for 1 minute

Mechanical:

- Operating Temperature:-40℃~+85℃
- Storage Temperature: -40℃~+85℃
- Durability : 750 Mating Cycles MIN.

Material:

- Housing:Thermoplastic UL94V-0
- Contact:0.45mm Dia Phosphor Bronze C51000
Plated Gold Over Ni

Wave Soldering: 260+/-5℃,5 sec max;
Resistance to solder : 260+/-5℃,10 +/- 1sec
packaging:Tray

LED SCHEMATIC

LEFT LED			RIGHT LED		
颜色	脚位	波长 (nm)	颜色	脚位	波长 (nm)
Yellow	Yellow 11 $\rightarrow$ 12	Yellow:585-595	Green	Green 9 $\rightarrow$ 10	Green:563-575

P/N: 102008-021121

02:RJ45

SERIES NUMBER

XX: 001~999


SERIES NO.1,2,3...
LED COLOR:SEE TABLE
CONTACT PLATED
1: G/F AU
TAIL SOLDER PLATED
1: G/F AU
PACKAGING:2:TRAY

MAGNETIC:0:NON

LED COLOR P/N TABLE


LED ITEM	Left	Right
0	Non	Non
1	Green	Yellow
2	Yellow	Green
3	Green/Yellow	Green/Yellow
4	Green/Orange	Green/Orange
5	Green	Green/Yellow
6	Green	Green/Orange

P.C.B LAYOUT TOP VIEW
Tolerance: ± 0.05


TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD									
X.X ±0.30	X.* ±10°	PART NO.		TITLE: RJ45 1X1 8P8C Tab Up W/O Shell W LED Lock TYPE									
.XX ±0.20	.X* ± 8°												
.XXX ±0.10	.XX* ± 5°												
UNITS	mm	DESIGN: Arvin		DRAWG NO. C-102008									
MATERILA		CHED:											
FINISH		APPD:		 <table><tr><td>SCALE</td><td>SHEET</td><td>REV.</td></tr><tr><td>1:1</td><td>1/3</td><td>A</td></tr></table>				SCALE	SHEET	REV.	1:1	1/3	A
SCALE	SHEET	REV.											
1:1	1/3	A											

- 1-1. 將成品放入底盤凹槽中, 並注意成品擺放方向的一致性(如示意圖一);
- 1-2. 每盤TRAY放滿100PCS成品, 注意不可少放或錯放;


- 2-1. 將每盤裝入成品的底盤(如示意圖一), 蓋上上蓋, 再依照《貼標規範》要求粘貼標籤;
- 2-2. 成品置於TRAY中, 注意TRAY(一上蓋配置一底盤)堆疊需朝同一方向(成品外觀形狀一致)擺放. 相疊至10层(共1000PCS)如示意圖三.



示意圖一
底盒
100PCS/盤




示意圖二
上蓋




示意圖三

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: RJ45 1X1 8P8C Tab Up W/O Shell W LED Lock TYPE			
.XX ±0.20	.X.* ± 8°		DRAWG NO. C-102008			
.XXX ±0.10	.XX.* ± 5°					
UNITS	mm	DESIGN: Arvin		SCALE	SHEET	REV.
MATERILA		CHED:		1:1	2/3	A
FINISH		APPD:				


- 3-1. 將產品套入防水袋, 再放入1包乾燥劑. 將防水袋整齊折合, 如示意圖四;
- 3-2. 將產品裝入紙箱, 如示意圖五;
- 3-3. 用膠帶把紙箱封合, 如示意圖六, 並按《貼標規範》要求粘貼標籤;



示意圖四



示意圖五



示意圖六

膠帶

条码标签 (具体样式依客户标准)

包 裝 容 量		
PCS/TRAY	PCS/內箱	PCS/外箱
100	/	1000

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.		TITLE: RJ45 1X1 8P8C Tab Up W/O Shell W LED Lock TYPE			
.XX ±0.20	.X* ± 8°						
.XXX ±0.10	.XX* ± 5°						
UNITS	mm	DESIGN: Arvin		DRAWG NO. C-102008			
MATERILA		CHED:					
FINISH		APPD:		SCALE 1:1 SHEET 3/3 REV. A			