



Recommended
P.C. Board Hole Layout



Cir- cuits	Dimension (mm)	
	L1	L2
2×2	2.00	4.00
2×3	4.00	6.00
2×4	6.00	8.00
2×5	8.00	10.00
2×6	10.00	12.00
2×7	12.00	14.00
2×8	14.00	16.00
2×9	16.00	18.00
2×10	18.00	20.00
2×11	20.00	22.00
2×12	22.00	24.00
2×13	24.00	26.00
2×14	26.00	28.00
2×15	28.00	30.00
2×16	30.00	32.00
2×17	32.00	34.00
2×18	34.00	36.00
2×19	36.00	38.00
2×20	38.00	40.00
2×21	40.00	42.00
2×22	42.00	44.00
2×23	44.00	46.00
2×24	46.00	48.00
2×25	48.00	50.00
2×26	50.00	52.00
2×27	52.00	54.00
2×28	54.00	56.00
2×29	56.00	58.00
2×30	58.00	60.00
2×31	60.00	62.00
2×32	62.00	64.00
2×33	64.00	66.00
2×34	66.00	68.00
2×35	68.00	70.00
2×36	70.00	72.00
2×37	72.00	74.00
2×38	74.00	76.00
2×39	76.00	78.00
2×40	78.00	80.00

Specifications

Current Rating : 2 Amps

Insulator Resistance : 1000 Megohms min.

Contact Resistance : 20 m ohms max.

Dielectric Withstanding : AC 500V

Operating Temperature : -40°C ~ +105°C

Contact Material : Brass

Insulator Material : Polyester, UL 94V-0-PA6T

Contact Plated : See Option

Standard:Full Gold Flash

		new		2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.		DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	2005WR-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25
			MODEL NAME	2005WR-2xXXP			X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xxx	±0.15	ANGULAR