


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- 技术指标(Technical Index):
- 1.工作温度(Temperature range):-25℃~+85℃.
 - 2.额定电压(Rated voltage):50V DC/AC(rms).
 - 3.额定电流(Rated current):0.7A(DC/AC).
 - 4.耐压值(Dielectricwithstanding voltage):500V AC/minute.
 - 5.绝缘电阻(Insulation resistance):≥1000MΩ.
 - 6.适用线规(Apply to gauge):AWG#26~#30.
 - 7.适用基板厚度(Applicable PC board thickness):1.2~1.6mm.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE:		
X.X±0.20		B-SZN1.5-2DP2		SZN1.5 WTB直插板端子		
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olivia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	1/1
FINISH	— — —					