



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

1.MATERIAL:

HOUSING:LCP 30% G/F UL94V-0

COLOR:BLACK

CONTACT:BRASS T=0.25mm

2.FINISH:

CONTACT:GOLD FLASH PLATING ON CONTACT AREA

100u"MIN.TIN PLATING ON SOLDER TAILS

50u"MIN.NICKEL UNDERPLATING OVER ALL

BOARD LOCK:100u"MIN.TIN PLATING ON SOLDER TAILS

50u"MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:






CURRENT RATING:1.5 AMPERE PER CONTACT

CONTACT RESISTANCE:30 mΩ MAX



INSULATION RESISTANCE:1000 MΩ MIN

DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40°C ~ +85°C



RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 15P公座90度	
.XX±0.20	.XX°±2°	JXT-SATA01-GS15P	DIP型带鱼叉针长2.30mm	
.XXX±0.05	.XXX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---			SCALE SHEET N:A 1/1