



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- 技术指标(Technical Index):
- 1.工作温度(Temperature range):-25°C~+85°C.
 - 2.额定电压(Rated voltage):250V DC/AC(rms).
 - 3.额定电流(Rated current):2.5A(AWG#22).
 - 4.耐压值(Dielectricwithstanding voltage):1000V AC/minute.
 - 5.绝缘电阻(Insulation resistance):≥1000MΩ.
 - 6.适用线规(Apply to gauge):AWG#22~#26.
 - 7.适用基板厚度(Applicable PC board thickness):1.2~1.6mm.



序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.50	±1°	PART NO.		TITLE:		
X.X±0.20		B-JC2.5-2DP2		JC25 WTB弯插板端子		
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	1/1
FINISH	— — —					