






Kinghelm®

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
AO.	/	新版发行	24.12.20	



材料及电镀

- ①. 塑件主体: PA66, UL94V-0
- ②. 焊 针: 黄铜, 镀镍

电气性能

额定电压: 300V
额定电流: 15A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC1500V\1Min

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ , 5秒

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

公差参数:

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50

X. xxx ±0.15
X. xx ±0.25
X. x ±0.35


NAME:

接线端子5.08开口弯针

P/N: KH-ZBF4000R-**P-5.08G-1
(**代表P数)

DWG NO:

THIRD ANGLE PROJECTION



UNIT:	SCALE	SIZE:	SHEET:	REV.
MM	1:1	A4	1/1	A1

DRAWN:

CHECKED:

APPROVED: