



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- 技术指标(Technical Index):
- 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
 - 额定电压(Rated voltage):250V DC/AC(rms).
 - 额定电流(Rated current):2.0A AC,DC.
 - 耐压值(Dielectricwithstanding voltage):1000V AC/minute.
 - 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
 - 适用线规(Apply to gauge):AWG#24~#28.
 - 适用基板厚度(Applicable PC board thickness):1.2~1.6mm.



序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X. ± 0.50	$\pm 1^{\circ}$	PART NO.	TITLE:	
X.X ± 0.20		B-JC2.0-2DP2		JC20 WTB弯插板端子
X.XX ± 0.10		DESIGN:	Ethan	MANUFACTURE DWG
UNITS	mm	CHED:	Olvia	SCALE N:A
MATERILA	---	APPD:	Ava	
FINISH	---			SHEET 1/1