




SPECIFICATION:

1.MATERIAL:

HOUSING: LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:


CONTACT:1u" GOLD PLATING ON CONTACT AREA


100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求			
3	Peg	Brass C2680		Tin/Ni Plated	
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V-0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X*±3°	PART NO.	TITLE: SATA 7+15P 母座		
.XX±0.20	.XX*±2°	JXT-SATA02-A2-M22PS	SMT H:6.74 板下型侧插		
.XXX±0.05	.XXX*±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1