

Kinghelm®

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/	新版发行	24.12.20	

材料及电镀





- ①. 塑件主体: PA66, UL94V-0
②. 焊 针: 黄铜, 镀镍

电气性能


额定电压: 300V
额定电流: 15A
接触电阻: $20\text{m}\Omega$ (Max)
绝缘电阻: $500\text{M}\Omega$ \DC500V
耐 电 压: AC2000V\1Min

机械性能

温度范围: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
瞬时温度: $+250^{\circ}\text{C}$, 5秒



PCB LAYOUT



深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160

公差参数:

Poles	Dim	Dim P	Dim L
2-6P		± 0.10	± 0.20
7-12P		± 0.20	± 0.30
13-18P		± 0.25	± 0.40
19-24P		± 0.30	± 0.50

未注明公差:

X. xxx ± 0.10
X. xx ± 0.20
X. x ± 0.30

NAME:

接线端子5.08开口直针

P/N: KH-F490V-**P-5.08G-1
(**代表P数)

DWG NO:

THIRD ANGLE PROJECTION



DRAWN:

UNIT:	SCALE	SIZE:	SHEET:	REV.
MM	1:1	A4	1/1	A1

CHECKED:

APPROVED: