









RoHS
Compliant



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

X.	±0.50	X.*	±2°	UNITS	广东创粤科技有限公司			
.X	±0.30	.X.*	±1°	mm				
.XX	±0.10	.XX.*	±0.5°	MAT'L	TITLE:			
.XXX	±0.05				Typec 16pin 沉板1.6 L=7.35MM沉板			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD					TYPE-C-16P-R1.6L7.35-30141	DWG NO.:		
					FINISH	CHKD:		
					Q'TY	DR:		
						SCALE	SHEET	REV.
						1/1	1/1	A1

- 备注:
1. 材质:
 - 1.1胶芯: LCP+30%G. F UL94V-0
 - 1.2端子: 黄铜C2680 : 镍底40U” MIN
接触区域镀金 (AU 0.8u”) 焊接区域镀金G/F
 - 1.3外壳: SUS201, T=0.30mm: 表面镀镍40U” MIN
 - 1.4中夹片: SUS201:
 2. 主要特性:
 - 2.1额定电流: 3A
 - 2.2接触阻抗: 40mΩ MAX (初始值)
50mΩ MAX (测试后)
 - 2.3绝缘阻抗: 100MΩ MIN
 - 2.4耐压测试: 100V AC R M S
 - 2.5整体插入力: 5-20N 整体插入力: 5-20N (耐久后)
整体拔出力: 8-20N 整体拔出力: 6-20N (耐久后)
 - 2.6耐久: 10000次
 - 2.7耐高温: SMT回流焊 (峰值260° ±5°), 塑胶不能有起泡, 融胶等不良, 变色, 翘曲变形在公差范围以内。
 - 2.8产品须做焊锡测试, 粘锡面积达到95%以上:
 - 2.9盐雾测试: 24H MIN
 - 2.10工作温度: -25℃~+80℃

REV.	ZONE	DESCRIPTION		DESIGN	DATE
B		NEW			
A1		GND	B12	GND	
A4		VBUS	B9	VBUS	
A5		CC1	B8	SBU2	
A6		DP1	B7	DN2	
A7		DN1	B6	DP2	
A8		SBU1	B5	CC2	
A9		VBUS	B4	VBUS	
A12		GND	B1	GND	
PIN		SIGNAL NAME	PIN	SIGNAL NAME	