







1. MECHANICAL: MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.

50 m Ω MAX AFTER 10000 CYCLES

4. Salt Spray:48H




X. ± 0.50	X* ± 2°	UNITS mm
.X ± 0.30	.X* ± 1°	
.XX ± 0.10	.XX* ± 0.5°	MAT'L /
.XXX ± 0.05		FINISH /
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYE TECHNOLOGY CO., LTD.		Q'TY /

TITLE:	TYPE C 16PIN 全贴母座
--------	-------------------


TYPE-C-16P-L7.35SMT-31440	DWG NO.:
---------------------------	----------

DR:








REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




包装示意图:



备注

- 1.把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包1000PCS),卷装完成后需用上带缠绕最少19CM;
- 2.在卷装OK的每卷盘面的指定位置上贴上物料和RoHS标签装入纸箱内;每箱装10盘
- 3.纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
- 4.如果客户对包装标签另有要求,请按客户要求作业;有未满之零数箱需用缓冲材料填充;
- 5.上载带剥离力0.2-1.2N.;



将10盘产品放入纸箱内

纸箱规格:
34.0X34.0X30.5CM

X. ±0.50	X.* ±2°	UNITS	广东创粤科技有限公司		
.X ±0.30	.X* ±1°	mm			
.XX ±0.10	.XX* ±0.5°	MAT'L	TITLE: 卷带10盘+产品10 K装		
.XXX ±0.05					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD:	DWG NO.:	
			CHKD:		
		Q'TY	DR:		
				SCALE	SHEET
				1/1	1/1
				REV.	A1