











RECOMMENDED P.C.B PATTERN LAYOUT



- Note:
- Material:
 - Housing: thermoplastic high temp.UL94V-0; Color: natural.
 - Latch: thermoplastic high temp.UL94V-0; Color: natural or black.
 - Terminal: copper alloy.
 - Fitting Nail: copper alloy.
 - Finish:
 - Terminal:
Underplating: Matte TIN 100u" MIN. And NICKEL 50u" Min
 - Fitting Nail:
Underplating: Matte TIN 100u" MIN. And NICKEL 50u" Min
 - Product must comply RoHS specification.
 - PART NO. SPECIFICATION: 5001-FCB 10 20-** R 1-00



RECOMMENDED FFC/FPC DIM.

PIN数	DIM=A	DIM=B	DIM=C	DIM=D
3P	2.00	4.10	7.0	7.1
4P	3.00	5.10	8.0	8.1
5P	4.00	6.10	9.0	9.1
6P	5.00	7.10	10.0	10.1
7P	6.00	8.10	11.0	11.1
8P	7.00	9.10	12.0	12.1
9P	8.00	10.10	13.0	13.1
10P	9.00	11.10	14.0	14.1
11P	10.00	12.10	15.0	15.1
12P	11.00	13.10	16.0	16.1
13P	12.00	14.10	17.0	17.1
14P	13.00	15.10	18.0	18.1
15P	14.00	16.10	19.0	19.1
16P	15.00	17.10	20.0	20.1
17P	16.00	18.10	21.0	21.1
18P	17.00	19.10	22.0	22.1
19P	18.00	20.10	23.0	23.1
20P	19.00	21.10	24.0	24.1
21P	20.00	22.10	25.0	25.1
22P	21.00	23.10	26.0	26.1
23P	22.00	24.10	27.0	27.1
24P	23.00	25.10	28.0	28.1
25P	24.00	26.10	29.0	29.1
26P	25.00	27.10	30.0	30.1
27P	26.00	28.10	31.0	31.1
28P	27.00	29.10	32.0	32.1
29P	28.00	30.10	33.0	33.1
30P	29.00	31.10	34.0	34.1
31P	30.00	32.10	35.0	35.1
32P	31.00	33.10	36.0	36.1
33P	32.00	34.10	37.0	37.1
34P	33.00	35.10	38.0	38.1
35P	34.00	36.10	39.0	39.1
36P	35.00	37.10	40.0	40.1
37P	36.00	38.10	41.0	41.1
38P	37.00	39.10	42.0	42.1
39P	38.00	40.10	43.0	43.1
40P	39.00	41.10	44.0	44.1

深圳市文章济美科技有限公司

UNLESS OTHERWISE SPECIFIED				APPROVED	DATE	PART NO
TOLERANCES ARE				CHECKED	DATE	5001-FCB1020-**R1-00-B
X.X ±0.25				DRAWING NO		JB96*11003
X.XX ±0.15				COMPUTER NO		RD1100301
X.XXX ±0.10				DATE		2013/03/28
ANG. ±0°30'				SCALE		8:1
UNIT				SIZE		A3
SER				NAME		FPC 10 CONNECTOR H2.0
AREA				ZIF FOR SMT(BOTTOM CONT)		REV A
REVISIONS				CHK		DATE
MM				UNIT		MM