




SPECIFICATION:

1. MATERIAL:

HOUSING: LCP/PA9T COLOR:BLACK
CONTACT:BRASS C2680R-H, T=0.25mm
PEG: BRASS C2680R-H, T=0.30mm

2. FINISH:

CONTACT: 1u"/3u"/5u"/5u" GOLD PLATING ON CONTACT AREA
100u" MIN. TIN PLATING ON SOLDER TAILS
30u" MIN. NICKEL UNDERPLATING OVER ALL
PEG: 100u" MIN. TIN PLATING ON SOLDER TAILS
30u" MIN. NICKEL UNDERPLATING OVER ALL

SECTION A-A

PCB LAYOUT

SECTION B-B

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Brass C2680		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7P 公座B型 全包 开窗鱼叉 侧插式针长2.05mm	
.XX±0.20	.XX°±2°	HMT-SATA07G-S02	CUSTOMER	SIZE
.XXX±0.05	.XXX°±0.5°	DESIGN: James		UNITS
MANUFACTURE DWG		CHED: Talen	SCALE	SHEET
		APPD: Sophia		1/1