






REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC, LCP UL94 V-0.
 - CONTACTS: COPPER ALLOY C2680
 - SHELL MID PLATE: STAINLESS STEEL SUS304
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u" MIN. UNDER PLATED OVER ALL.
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.
 - (GOLD PLATING THICKNESS FOLLOW THE P/N)
 - GOLD FLASH PLATING ON SOLDER AREA
 - FRONT SHELL:
 - Ni 30u" MIN. UNDER PLATED OVER ALL.
- MECHANICAL PERFORMANCE,
 - INSERTION FORCE: 0.5~2.0kgf.
 - REMOVAL FORCE: 0.8kgf~2.0kgf.
 - DURABILITY: 10000 CYCLES.
- ELECTRICAL PERFORMANCE,
 - CURRENT RATING: 5A
VOLTAGE RATING: 20V
 - INSULATION RESISTANCE: 100MΩ MIN
 - CONTACT RESISTANCE: 30mΩ MAX
 - DIELECTRIC WITHSTAND VOLTAGE, AC 100V FOR 1 MINUTE.
- ENVIRONMENTAL PERFORMANCE:
 - OPERATING TEMPERATURE: -30° C~+85° C.
- IR REFLOW:
 - THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C.
- ROHS REACHER.

X. ±0.50	X.* ±2°	UNITS	深圳市创粤科技有限公司	
.X ±0.30	.X* ±1°	mm		
.XX ±0.10	.XX* ±0.5°	MAT'L	TITLE:	
.XXX ±0.05			TYPE-C 16PIN沉板2.4MM母座 长L=6.50MM	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	TYPE-C-16P-R2.4L6.5-04008 DWG NO.:	
		Q'TY	CHKD:	
			DR:	
			SCALE SHEET REV.	
			1/1 1/1 A1	




RoHS
Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME
A1	GND
A4	VBUS
A5	CC1
A6	Dp1
A7	Dn1
A8	SBU1
A9	VBUS
A12	GND


PIN NUMBER	SIGNAL NAME
B12	GND
B9	VBUS
B8	SBU2
B7	Dn2
B6	Dp2
B5	CC2
B4	VBUS
B1	GND



X. ± 0.50	X.* $\pm 2^\circ$	UNITS mm	深圳市创粤科技有限公司
.X ± 0.30	.X* $\pm 1^\circ$		TITLE:
.XX ± 0.10	.XX* $\pm 0.5^\circ$	MAT'L	TYPE-C 16PIN沉板2.4MM母座 长L=6.50MM
.XXX ± 0.05			TYPE-C-16P-R2.4L6.5-04008
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	DWG NO.:
		Q'TY	CHKD:
			DR:
			SCALE SHEET REV. 1/1 1/1 A1




REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



NOTES




1. 越沟 擇僅
LEAD TAPE LENGTH
堤蹋源研
PULL OUT DIRECTEON

堤蹋源研
PULL OUT DIRECTEON



2. 上帶 剝力力為: 0.1~1.3N(10.2gf~130gf)
PEELING OFF FORCE OF TOP TAPE: 0.1~1.3N(10.2gf~130gf)
出貨運輸過程中一定注意:
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT:
卷帶在運輸過程中不能散開
PEELING OFF SHOULD NOT BE ALLOWED DURING TRANSPORTATION

包裝明細表 (The detail of the packing) Carton					
包裝容量 (Packing Capacity)			重量 Weight (Kg)		
pcs/box	boxes/Carton	Pcs/Box	N. W. /Pcs	N. W. /Box	G. W. /Box
1000	10	10000	---	---	---



X. ±0.50	X.* ±2*	UNITS	深圳市创粤科技有限公司		
.X ±0.30	.X* ±1*	mm			
.XX ±0.10	.XX* ±0.5*	MAT'L	TITLE:		
.XXX ±0.05			TYPE-C 16PIN沉板2.4MM母座 长L=6.50MM		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD			FINISH		
			TYPE-C-16P-R2.4L6.5-04008 DWG NO.:		
			CHKD:		
			Q'TY		
			DR:		
			SCALE SHEET REV.		
			1/1 1/1 A1		