




技术指标:

- 1.温度范围: -25°C~85°C.
- 2.额定电压: 100V AC,DC.
- 3.耐电压: 500V AC/minute.
- 4.接触电阻: ≤20mΩ .
- 5.绝缘电阻: ≥500MΩ.
- 6.额定电流: 1A AC,DC.

材料:

- 1.塑胶: PA66 白色

PART NO	PIN	A	B	C	D
WF-ZH1.5-2PC-MB	2	1.50	4.82	3.66	4.50
WF-ZH1.5-3PC-MB	3	3.00	6.32	5.16	6.00
WF-ZH1.5-4PC-MB	4	4.50	7.82	6.66	7.50
WF-ZH1.5-5PC-MB	5	6.00	7.90	8.16	9.00
WF-ZH1.5-6PC-MB	6	7.50	9.40	9.66	10.50
WF-ZH1.5-7PC-MB	7	9.00	10.90	11.16	12.00
WF-ZH1.5-8PC-MB	8	10.50	12.40	12.66	13.50
WF-ZH1.5-9PC-MB	9	12.00	13.90	14.16	15.00
WF-ZH1.5-10PC-MB	10	13.50	15.40	15.66	16.50
WF-ZH1.5-11PC-MB	11	15.00	16.90	17.16	18.00
WF-ZH1.5-12PC-MB	12	16.50	18.40	18.66	19.50
WF-ZH1.5-13PC-MB	13	18.00	19.90	20.16	21.00
WF-ZH1.5-14PC-MB	14	19.50	21.40	21.66	22.50
WF-ZH1.5-15PC-MB	15	21.00	22.90	23.16	24.00
WF-ZH1.5-16PC-MB	16	22.50	24.40	24.66	25.50

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®	
DIM. X. X.X X.XX GENERAL ANGLE: ±1°	TITLE: ZH1.5 母座胶壳 不带扣 白色		DWG. NO.: WF-ZH1.5-XPC-MB		CHECKED: MAX
	PART NO.: WF-ZH1.5-XPC-MB		DWG. SIZE: A4		DRAWN: ELLA
	UNIT: mm		SCALE: none		APPROVED: WILL
	SHEET: 1 of 1		LAYER: bxconn		