


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN	James		9/26

250±2



NOTES:

- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
 - SEE TABLE
- ALL COMPONENTS ARE ROHS COMPLIANT.

深圳市金航标电子有限公司

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	端子	国产I-PEX 1.13端子，镀金	1
③	套管	OD:4.5* 35 mm 黑色热缩套管	1
②	铜管	铜管： 5.2*24mm, 1.13线用	1
①	同轴线	RF1.13黑色色同轴线， OD:1.13mm	AS
ALL DIMENSION ARE IN MM		DATE	
DRAWN James		2026-08-16	
CHKD Frank		2026-08-16	
APPD Scott		2026-08-16	
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING		TITLE KH1NB(2.4G)C250-03-A.3	
PROJECTION		铜管天线	
GENERAL TOLERANCE FOR ANGLES XX XXX X.XXX ±1° ±0.3 ±0.25 ±0.150		DWG Number:	
SIZE B		REV A	
SCALE:Free		TYPE	
SHEET 1 OF 1			

CUSTOMER PIN:

D

C

B

A

4

3

2

1

D

C

B

A

4

3

2

1